

## USB 2.0 Hi-Speed A/B Active Repeater Cable (M/M), 25-ft.

MODEL NUMBER: **U042-025**



### Description

Tripp Lite's High-Speed USB 2.0 Active A-B cable overcomes the 5-meter USB distance limitation with an active repeater in the middle of the cable. Now USB printers and other devices can be located up to 25-ft. away from the computer in a single, non-daisychainable run, with no need for extension cables. Full 480Mbps speed is maintained along the entire length of the cable. Backward compatible to USB 1.1. Plug-and-play, Windows and MAC compatible. The U042-025 provides up to 150mA of power to the connected device. If your device requires more than 150mA of power, it will either need to have its own power supply; or, to be plugged into a powered USB 2.0 hub (such as [U222-007-R](#)) that is connected to the U042-025.

### Features

- Connect a computer to a printer or other USB device up to 25-ft. away
- High-Speed USB 2.0 and USB 1.1 compatible
- Active repeater maintains 480Mbps signal integrity
- USB "A" to USB "B" connections
- Windows 98/ME/2000/XP/Vista/WIN7/8 and MAC compatible
- Cable length: 25-ft. Weight: 1 lb.
- Repeater Pod dimension: 16.75 x 57.3 x 31.7 (mm.) / 0.7 x 2.3 x 1.3 (in.)
- The U042-025 provides up to 150mA of power to the connected device. If your device requires more than 150mA of power, it will either need to have its own power supply; or, to be plugged into a powered USB 2.0 hub (such as [U222-007-R](#)) that is connected to the U042-025.

## Specifications

OVERVIEW	
Chromebook Compatible	Yes
Style	USB

### Highlights

- 25-ft. USB A-B Active Cable
- Overcomes the 5-meter USB barrier
- Built-in repeater maintains high-speed USB 2.0 signal quality

### System Requirements

- A USB 2.0 port and USB 2.0 device (with type B jack) are required to meet USB 2.0 speeds. A USB 1.1 port and/or device can be used, but you will not be able to achieve USB 2.0 speeds.
- The U042-025 provides up to 150mA of power to the connected device. If your device requires more than 150mA of power, it will either need to have its own power supply; or, to be plugged into a powered USB 2.0 hub (such as [U222-007-R](#)) that is connected to the U042-025.

### Package Includes

- 25-ft. Hi-Speed USB 2.0 Active Cable



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
[www.tripplite.com](http://www.tripplite.com)

Model Type	Connectivity
Cable Types	USB
<b>OUTPUT</b>	
USB Charging	No
<b>INPUT</b>	
Cable Length (ft.)	25
Cable Length (m)	8
<b>PHYSICAL</b>	
Color	Silver
<b>CONNECTIONS</b>	
Connector A	USB A (MALE)
Connector B	USB B (MALE)
Number of Connectors	2
<b>WARRANTY</b>	
Product Warranty Period (Worldwide)	1-year limited warranty

© 2015 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.