

USB 2.0 to HDMI Dual or Multi Monitor External Video Graphics Card Adapter, 128 MB SDRAM - 1920x1200,1080p

MODEL NUMBER: U244-001-HDMI-R



Description

Tripp Lite's U244-001-HDMI-R USB to HDMI Multi Monitor External Video Adapter allows you to connect an additional monitor or HDTV to a computer/laptop's USB 2.0 port. Up to six adapters can be used simultaneously, allowing the user to connect up to six additional monitors/TV's to a single computer. Once the installation is done, the computer screen appears on the add-on monitor(s) without the hassle of function keys to swap to a second monitor. Supports HD resolutions up to 1080p (60Hz). Windows and Intel Mac compatible.

Features

- Add an additional HDMI monitor or TV through a single USB 2.0 port
- Hot pluggable; add or remove a monitor without the need for a system reboot
- Compatible with Windows XP, Vista, 7, 8, and 8.1. Supports both 32- and 64-bit.
- Supports Surface tablets running non-RT Windows 8 and 8.1
- Compatible with Intel Mac OS X 10.8 (10.8.3 and later), 10.9 and 10.10 (Mac OS X 10.9 and 10.10 is limited to a single add-on monitor. See driver Release Notes for details) Supports both 32- and 64-bit.
- Use up to six adapters simultaneously, adding up to six additional monitors to a single computer
- View large spreadsheets across multiple screens by extending video amongst all monitors
- Play video on one monitor while working on another
- Do multiple screen presentations from a laptop computer
- Bus powered...no external power adapter needed
- Features 128MB DDR SDRAM of memory
- Supports HD resolutions up to 1080p (60Hz)
- Uses DisplayLink DL165 chipset

Specifications

Highlights

- Connect a PC or Laptop to an HDTV with HDMI
- Windows and Intel Mac compatible
- Features 128MB DDR SDRAM of memory
- Supports HD resolutions up to 1080p (60Hz)

Applications

Office workstation

- View large spreadsheets across multiple screens
- Multitask more effectively without overlapping windows
- Edit on one screen while surfing the Internet for information on the other

On the road

- Do multiple screen presentations without bringing another computer
- Easily provide multiple screen exhibitions in a trade show

Graphics workstation

- Use second display for palettes/tools
- Get a panoramic view of large documents

Editing workstation

- Type documents on one screen while viewing reference material on the other
- Compare two documents simultaneously across two screens

Financial analysis

- Have one monitor per data stream
- View charts and live data at the



OVERVIEW	
Chromebook Compatible	No
Display Style	Adapter
Model Type	HDMI
CONNECTIONS	
Connector A	USB A (MALE)
Connector B	HDMI (FEMALE)
WARRANTY	
Product Warranty Period (Worldwide)	1-year limited warranty

© 2015 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.

same time

Entertainment

- View videos/TV on one screen and reviews on the other
- Get additional perspectives when playing games

System Requirements

- USB 2.0 port
- HDMI monitor or TV
- Compatible with Windows XP, Vista, 7, 8, and 8.1. Supports both 32- and 64-bit.
- Supports Surface tablets running non-RT Windows 8 and 8.1
- Compatible with Intel Mac OS X 10.8 (10.8.3 and later), 10.9 and 10.10 (Mac OS X 10.9 and 10.10 is limited to a single add-on monitor. See driver Release Notes for details) Supports both 32- and 64-bit.
- Reference the owner's manual for system requirements when using multiple adapters or when using the add-on monitor for DVD playback.

Package Includes

- U244-001-HDMI-R USB to HDMI Multi Monitor External Video Adapter
- 3 ft. USB Cable
- Quick Start Guide
- Driver CD with Owner's Manual