

## USB 3.0 SuperSpeed Active Repeater Cable (AB M/M), 25-ft.

MODEL NUMBER: **U328-025**



### Description

Tripp Lite's SuperSpeed USB 3.0 Active A-B cable overcomes the 5-meter USB distance limitation with an active repeater in the middle of the cable. Now USB printers and other devices can be located up to 25-ft. away from the computer in a single, non-daisychainable run, with no need for extension cables. Full 5Gbps speed is maintained along the entire length of the cable. Backward compatible to USB 1.1 and 2.0 . Plug-and-play, Windows and MAC compatible.

### Features

- Connect a computer to a printer or other USB device up to 25-ft. away
- SuperSpeed USB 3.0, Hi-Speed 2.0 and USB 1.1 compatible
- Active repeater maintains 5Gbps signal integrity
- USB "A" to USB "B" connections
- Windows 98/ME/2000/XP/Vista/WIN7/8 and MAC compatible
- Cable length: 25-ft. Weight: 1 lb.
- Repeater Pod dimension: 16.75 x 57.3 x 31.7 (mm.) / 0.7 x 2.3 x 1.3 (in.)

### Highlights

- 25-ft. USB3.0 SuperSpeed A-B Active Cable
- Overcomes the 5-meter USB barrier
- Built-in repeater maintains SuperSpeed USB 3.0 signal quality

### System Requirements

- A USB 3.0 port and USB 3.0 device (with type B jack) are required to meet USB 3.0 speeds. A USB 2.0 or 1.1 port and/or device can be used, but you will not be able to achieve USB 3.0 speeds.

### Package Includes

- 25ft. SuperSpeed USB3.0 A/B Active Device Cable (A Male to B Male)

## Specifications

| OVERVIEW              |        |
|-----------------------|--------|
| Chromebook Compatible | Yes    |
| Style                 | USB    |
| Model Type            | Cables |



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
[www.tripplite.com](http://www.tripplite.com)

|                                     |                         |
|-------------------------------------|-------------------------|
| Cable Types                         | USB                     |
| <b>OUTPUT</b>                       |                         |
| USB Charging                        | No                      |
| <b>INPUT</b>                        |                         |
| Cable Length (ft.)                  | 25                      |
| Cable Length (m)                    | 8                       |
| <b>PHYSICAL</b>                     |                         |
| Color                               | Black                   |
| <b>CONNECTIONS</b>                  |                         |
| Connector A                         | USB 3.0 A (MALE)        |
| Connector B                         | USB 3.0 B (MALE)        |
| <b>WARRANTY</b>                     |                         |
| Product Warranty Period (Worldwide) | 1-year limited warranty |

© 2015 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.