



### Fibre Optic Preparation Fluid



This optical-grade solvent is double-filtered for purity, so cleaning is more consistent and reliable. It delivers excellent results removing light oils, salts, moisture, fingerprints, dust, lint, fibres, grime, polishing media and uncured epoxies. This versatile cleaner is safe on glass, metal, cured epoxies, and insulators; it is generally safe on plastics except plastic optical fibres (see Fibre Optic High Performance Cleaving Tool under “Related Products”).

The Fibre Prep Fluid out-cleans IPA because it is a stronger solvent and it dries faster. The dense solvent “floats” particulate off surfaces and dissipates static bonds. This makes it perfect for “Wet/Dry” cleaning of connector endfaces. When terminating or fusion splicing, it cleans both single-strand and ribbon fibre and “squeaks” when the fibre is clean.

The hermetically-sealed container uses the unique Triton™ 3-way dispensing system, the most versatile packaging system in the industry. The spill-proof, sealed canister also prevents refilling and cross-contamination, ensuring clean solvent every time. The canister also is “TravelSAFE™” that is, the pump spray is “nonhazardous, nonregulated” so it can be shipped, even by air, without extra paperwork or hazmat fees. With over 400 fast and reliable cleanings per canister, Fibre Prep Fluid reduces installation cleaning costs to only pennies.

#### FEATURES

- Nonhazardous Optical-Grade Solvent
- Ideal for “Wet/Dry” Connector End-Face Cleaning
- Ideal for Cleaning Bare Fibre
- Safe on Glass, Metal, Epoxies and Circuit Boards
- Dissipates Static Charges
- Easy Shipping - Nonhazardous
- Formulation Avoids Hazmat Issues

#### SPECIFICATION

##### PRODUCT DESCRIPTION

Chemical Family HPC Solvent  
Appearance Clear Colourless Liquid  
Odour Slight, Ethereal  
Boiling Point 45°C  
Flammability Nonflammable  
RoHS and WEEE Compliant  
Snap Approved

#### ORDERING INFORMATION

DESCRIPTION	PART NO.
Fibre Preparation Fluid 3.oz Pump Bottle	FPF03M/Z

Please contact our sales team on +44 (0) 1908 441 121 for further ordering information.

**CONTACT OUR SALES TEAM TODAY**

**Europe:** +44 1908 441 100 | [sales@optronicsnet.com](mailto:sales@optronicsnet.com)

**Americas:** +1 410 242 9026 | [sales@optronicsnet.com](mailto:sales@optronicsnet.com)

**Asia Pacific:** +86 755 2531 3694 | [apac@optronicsnet.com](mailto:apac@optronicsnet.com)

**Middle East & Africa:** +971 4 443 1028 | [mea@optronicsnet.com](mailto:mea@optronicsnet.com)

**Web:** [www.optronicsnet.com](http://www.optronicsnet.com)

Downloaded from [www.optronicsnet.com](http://www.optronicsnet.com) | Information correct as of May 9, 2014 | Optronics reserves the right to make changes to the product specifications in this datasheet at any time without notice.  
All content © Optronics 2015