

IEEE 1284 AB Parallel Printer Cable (DB25 to Cen36 M/M), 10-ft.

MODEL NUMBER: **P606-010**



Description

Tripp Lite's 10-ft. IEEE 1284 A-B parallel printer cable connects computers with a DB25 female parallel port to parallel printers with a Centronics 36 female parallel port. It supports high-speed IEEE 1284 bi-directional communication. The cable features nickel plated DB25 male/Cent36 male connectors and gold plated copper contacts for superior conductivity. It is manufactured from superior molded cable with integral strain relief and double shielding for maximum EMI/RFI protection. It contains low-capacitance, impedance matched, twisted-pair conductors that protect against cross-talk and other transmission problems.

Features

- Supports high-speed IEEE 1284 bi-directional communication (modes: standard compatible nibble byte ECP and EPP)
- Length: 10-ft. Connectors: DB25 male/Cent36 male
- Nickel plated connectors and gold plated copper contacts offer superior conductivity
- Superior molded cable with integral strain relief and double shielding (foil and braid) for maximum EMI/RFI protection
- Low-capacitance impedance matched twisted-pair conductors protect against cross-talk and other transmission problems
- Bi-directional communication allows your printer to broadcast printer error messages back to network computers
- Molded ends with easy-grip textured overmold

Specifications

OVERVIEW	
Style	Printer Cables
Cable Types	PRINTER
INPUT	
Cable Length (ft.)	10

Highlights

- Superior molded cables with integral strain relief and foil-shielding for maximum EMI/RFI protection
- IEEE 1284 Printer Cables provide superior conductivity and support high-speed bi-directional printing

System Requirements

- Computers with a DB25 Female parallel port
- Parallel printers with a Centronics 36 Female parallel port with high-speed IEEE 1284 Bi-Directional communication (although not essential).

Package Includes

- 10-ft. IEEE 1284 AB Parallel Printer Cable DB25M to Cen36M



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Cable Length (m)	3.05
PHYSICAL	
Color	Black
CONNECTIONS	
Connector A	DB25 (MALE)
Connector B	CENTRONICS 36 (MALE)
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2015 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.