

AXIS F4005 Dome Sensor Unit

Recessed dome for discreet indoor surveillance

AXIS F4005 is a compact, easy-to-install recessed dome sensor unit for discreet indoor video surveillance in retail, office, and banking environments. For use with an AXIS F Main Unit, AXIS F4005 provides a 1080p resolution and a wide 113° horizontal field of view. It enables WDR – Forensic Capture when used with an AXIS F41 Main Unit. AXIS F4005 also supports Axis' Corridor Format to suit vertically oriented areas such as staircases, hallways and aisles. It comes with a 12-m (39 ft.) cable for connection to a main unit. A rotation tool is supplied for leveling the image.

- > Compact, recessed dome for indoor surveillance
- > Fixed lens with 1080p resolution
- > Wide 113° horizontal field of view
- > Supports Wide Dynamic Range Forensic Capture (with AXIS F41 Main Unit)
- > Supports Axis' Corridor Format







AXIS F4005 Dome Sensor Unit

Camera	
Image sensor	1/2.8" (effective) progressive scan RGB CMOS
Lens	2.8 mm, F2.0 With AXIS F41/F44 in 1080p: Horizontal angle of view 113°, Vertical angle of view 62° With AXIS F44 in 720p: Horizontal angle of view 73°, Vertical angle of view 41°
Minimum illumination	0.3 lux
Shutter time	With AXIS F41: HDTV 1080p 25/30/50/60 fps: 1/143000 s to 2 s; WUXGA (1920x1200) 25/30 fps: 1/143000 s to 2 s With AXIS F44: 1080p 12.5/15 fps: 1/22500 s to 2 s; HDTV 720p 25/30 fps: 1/28000 s to 2 s
Camera angle adjustment	Tilt: 120°
General	
Casing	Plastic
Operating conditions	-30 °C to 55 °C (-22 °F to 131 °F) Humidity 10-85% RH (non-condensing)

Storage conditions	-40 °C to 65 °C (-40 °F to 149 °F)
Approvals	ECE R10 rev.04, EN 50121-4, IEC/EN/UL 60950-1, IEC 60068-2-1, IEC 60068-2-2, IEC 60068-2-14, IEC 60068-2-30, IEC 60068-2-60, IEC 60068-2-78, IEC 62236-4, EN 55022 Class B, EN 55024, EN 61000-3-2, EN 61000-3-3, EN 61000-6-1, EN 61000-6-2, FCC Part 15 Subpart B Class B, ICES-003 Class B, VCCI Class B, C-tick AS/NZS CISPR 22 Class B, KCC KN22 Class B, KN24, EN 50581, IEC 60068-2-60, IEC 60721-3-5 5M3 (vibration, shock)
Dimensions	Depth: 38 mm (1 1/2 in) ø 112 mm (1/6 in) 12-m (39 ft) cable
Weight	530 g (1.1 lb)
Required hardware	AXIS F Main Unit
Included accessories	Installation Guide, Windows decoder 1-user license
Warranty	Axis 3-year warranty, see www.axis.com/warranty

More information is available at www.axis.com

