

UPS Replacement Battery Cartridge Kit (2 sets of 4) for select APC UPS

MODEL NUMBER: **RBC12A**



Description

Tripp Lite's premium UPS replacement battery cartridges breathe new life into UPS systems suffering from expired or weak internal batteries. Each replacement battery set is carefully configured to meet or exceed all of the original manufacturer specifications and ships pre-assembled and ready for installation into your UPS system. Reusable packaging holds expired batteries for recycling center delivery. Compatible with select UPS systems from APC and other major brands. See Tripp Lite's UPS replacement battery page to confirm compatibility and quantity required.

Features

- Restores your UPS to its original runtime specifications
- Comes pre-assembled and ready for installation into your UPS system
- Reusable packaging holds expired batteries for recycling center delivery
- Compatible with many brands and models, including APC models SU2200RM3U, SU3000RM3U, SU3000RMT3U, NS2200RM3U, NS3000RM3U, NS3000RMT3U, SU5000T, and SU5000RMT5U. NOTE: SU5000T and SU5000RMT5U require (2) RBC12A

Specifications

BATTERY	
Typical Battery Lifespan	3 - 5 years, depending on host UPS operating system
PHYSICAL	
Shipping Dimensions (hwd / in.)	7 x 12.5 x 15.5
Shipping Dimensions (hwd / cm)	17.8 x 31.8 x 39.4
Shipping Weight (lbs.)	50 lbs. (Package includes 2 sets of 2 batteries each weighing 22 lbs.)

Highlights

- Up to 30% longer runtime than basic replacements
- OEM certified premium batteries
- Rugged, leakproof construction
- Maintenance-free
- Wide operating temperature range

Applications

- Extends the operating life of older UPS systems
- Restores or enhances runtimes of UPS systems exhibiting reduced power failure runtime

Package Includes

- UPS battery replacement cartridge
- Instruction manual with installation, recycling and warranty information



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Shipping Weight (kg)	22.7 kg (Package includes 2 sets of 4 batteries each weighing 10 kg)
Unit Dimensions (hwd / in.)	3.6875 x 10.25 x 5.875
Unit Dimensions (hwd / cm)	Each set measures 9.4 x 26 x 14.9
Unit Weight (lbs.)	22
Unit Weight (kg)	10
ENVIRONMENTAL	
Relative Humidity	0 - 95% non-condensing
Operating Elevation (ft.)	0 - 10,000
Storage Elevation (ft.)	0 - 50,000
Operating Elevation (m)	0-3000 m
Storage Elevation (m)	0 - 15,200 m
WARRANTY	
Product Warranty Period (U.S. & Canada)	18-month limited warranty
Product Warranty Period (International)	1-year limited warranty
Product Warranty Period (Mexico)	1-year limited warranty
Product Warranty Period (Puerto Rico)	1-year limited warranty

© 2015 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.