

45U SmartRack 4-Post Open Frame Rack - Threaded 12-24 Mounting Holes

MODEL NUMBER: SR4POST1224



Highlights

- 45U 4-post open frame rack
- Black steel with threaded (12-24) mounted holes
- Toolless button holes to accept PDUs or cable managers

Package Includes

- SR4POST1224
- Installation hardware
- 50x pieces of 12-24 screws and washers
- Cable management hooks
- Owner's Manual with warranty information

Description

SmartRack 4-post open frame racks are ideal for cost conscious 19 inch rack mount applications. Multiple units can be bolted together side by side.

Features

- Supports 1000lbs of rackmount equipment
- Adjustable mounting depth (22 to 39 inches)
- Textured powder coat finish
- Heavy-duty cold-rolled steel construction
- Numbered mounting positions
- Bolt down provisions
- Threaded 12-24 holes
- Black finish
- Easy assembly

Specifications

OVERVIEW	
Style	4-Post
PHYSICAL	
Installed Whole System Maximum Rack Depth (in.)	39
Installed Whole System Maximum Rack Depth (cm)	99.06



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Installed Whole System Minimum Rack Depth (in.)	22
Installed Whole System Minimum Rack Depth (cm)	55.88
Rack Height (U Spaces)	45
Shipping Dimensions (hwd / in.)	85 x 6 x 4
Shipping Dimensions (hwd / cm)	215.9 x 15.24 x 10.16
Shipping Weight (lbs.)	70
Shipping Weight (kg)	31.5
Unit Dimensions (hwd / in.)	84.3 x 20.3 x 22-39.4
Unit Weight (lbs.)	69
Unit Weight (kg)	31.29
Unit Dimensions (cm)	214.12 x 51.56 x 55.9~100.1 (depth adjustable)
Color	Black
Weight Capacity - Stationary (lbs.)	1000
Weight Capacity - Stationary (kg)	453.6
Hinged (Swings Away from Wall Bracket)	No
SPECIAL FEATURES	
Grounding Lug	Includes a set of screws, bolts, and washers to secure a user-supplied grounding wire to Front and Back frames
CERTIFICATIONS	
NOM (Mexico)	Tested to NOM (Mexico)
Approvals	EIA-310-D, IEC 60297-3-100, DIN 41494, RoHS
WARRANTY	
Product Warranty Period (Worldwide)	5-year limited warranty

© 2015 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.