

Corded UPS Backplate Outlet Kit for SU6000RT3UHV UPS, 200/208/240V Input/Output, NEMA L6-30R

MODEL NUMBER: **SUPDM11**



Highlights

- Converts Tripp Lite's hardwire SU6000RT3UHV UPS system from hardware in/out to one with an AC plug and outlets
- 10 ft. / 3m AC input cord with NEMA L6-30P plug
- 2 NEMA L6-30R output receptacle
- Easy quick-connect wiring installs in minutes

Applications

- Ideal for applications calling for Tripp Lite's SU6000RT3UHV where plug-in AC input and output connections are required

Description

Tripp Lite's SUPDM11 corded backplate kit converts Tripp Lite's hardwire SU6000RT3UHV UPS system to one with an AC plug and outlet. 10 ft./3m input line cord with L6-30P plug enables connection to 200/208/240V 30A mains power. Two L6-30R output receptacles allow for the connection of high current equipment load or power distribution units (PDU). Easy quick-connect wiring installs in minutes.

Features

- Converts Tripp Lite's hardwire SU6000RT3UHV UPS system to one with an AC plug and outlet
- 10 ft./3m AC line cord with L6-30P input plug-in connection
- Two L6-30R output receptacles pass 200/208/240V output voltage on to connected equipment
- Easy quick-connect wiring installs in minutes

Specifications

| OVERVIEW | |
|------------------------|--------------|
| Model Type | Outlet Kits |
| Accessories Type | PDU Module |
| OUTPUT | |
| Output Receptacles | (1) L6-30R |
| Output Nominal Voltage | 200/208/240V |
| INPUT | |



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

| | |
|-------------------------------------|-------------------------|
| UPS Input Cord Length (ft.) | 10 |
| UPS Input Cord Length (m) | 3.05 |
| Recommended Electrical Service | 30A 200/208/240V |
| Input Connection Type | NEMA L6-30P |
| PHYSICAL | |
| Shipping Dimensions (hwd / in.) | 5.5 x 9 x 14.25 |
| Shipping Dimensions (hwd / cm) | 14 x 22.9 x 36.2 |
| Shipping Weight (lbs.) | 4.7 |
| Shipping Weight (kg) | 2.2 |
| Unit Dimensions (hwd / in.) | 3 x 3.75 x 4.75 |
| Unit Dimensions (hwd / cm) | 7.6 x 9.5 x 12.1 |
| Unit Weight (lbs.) | 4 |
| Unit Weight (kg) | 1.8 |
| Material of Construction | Steel |
| WARRANTY | |
| Product Warranty Period (Worldwide) | 2-year limited warranty |

© 2015 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.