

Protect It! 230V Surge Protector with 6 French/Belgian Outlets, 2M Cord, 1140 Joules, French plug

MODEL NUMBER: TLP61F



Highlights

- 6 safety outlet covers
- 2 m cord
- "Protected" LED
- 1140 joule rating

Applications

Ideal for home computers, printers, scanners, and desk lamps.

Package Includes

- TLP61F surge suppressor
- Instruction manual and warranty information

Description

Tripp Lite's Protect It!™ TLP61F offers economical AC surge suppression for full protection of 220-250V home computers, printers, scanners, and desk lamps. The TLP61F offers 6 French Type E outlets and a 2 meter AC line cord. Internal safety covers protect against accidental contact with unused outlets.

Features

- Protect It!™ TLP61F offers economical AC surge suppression
- 1140 joules AC surge suppression shields equipment from surges and line noise
- 6 French Type E outlets protects computers and peripherals
- 2 m cord with French plug
- Protected LED
- Internal safety covers protect against accidental contact with unused outlets

Specifications

OVERVIEW	
Style	Strip
OUTPUT	
Output Receptacles	(6) French/Belgian
Circuit Breaker (amps)	10
Transformer Accommodation	3
USB Charging	No



INPUT	
Nominal Input Voltage(s) Supported	230V AC
Recommended Electrical Service	230V (220-250V)
Input Connection Type	French
Input Cord Length (ft.)	6
Input Cord Length (m)	2
Voltage Compatibility (VAC)	220-250
USER INTERFACE, ALERTS & CONTROLS	
Diagnostic LEDs	Green Protected
SURGE / NOISE SUPPRESSION	
AC Suppression Joule Rating	1140
DATALINE SURGE SUPPRESSION	
Telephone/DSL Protection	No
Cable (Coax) Protection	No
Network (Ethernet) Protection	No
PHYSICAL	
Shipping Dimensions (hwd / in.)	17.10 x 4.53 x 2.17
Shipping Dimensions (hwd / cm)	43.43 x 11.51 x 5.51
Shipping Weight (lbs.)	1.30
Shipping Weight (kg)	0.59
Unit Dimensions (hwd / in.)	16 x 2.32 x 1.75
Unit Dimensions (hwd / cm)	40.64 x 5.89 x 4.45
Unit Weight (lbs.)	1.2
Unit Weight (kg)	0.54
Receptacle Color	Light Gray
Color (AC Line Cord)	Light Gray
Color	Gray
SPECIAL FEATURES	
Right-Angle Plug	Yes
WARRANTY	



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Product Warranty Period (Worldwide)	Lifetime limited warranty
-------------------------------------	---------------------------

© 2015 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.