



**Project:** Neptune  
**Location:** Horsham  
**Neptune**

**SNA Terminal Blocks**  
**T&B Catalog Number:**

019904225

**UPC Number:**

66201996460

**Status:**

Active

**Description:**

Gray, feed through terminal block with 8 mm spacing, 25 Amp rated UL current with both insulation displacement and screw clamp connections that accept 16 - 14 AWG wire range for IDC and 22 - 8 AWG wire range for screw clamp connection

**Features**

	Insulation displacement and screw clamp connection technology
	Insulation displacement technology is the fastest known connection type
	Self-locking clamp design prevents screw loosening
	Touch-safe IP20 protection
	High quality steel offers a very high over-torque resistance
	Compensates for the flattening of copper under contact pressure
	Clamp is protected from harsh environments by a zinc bichromate surface treatment

**Application**

	For use with applications ranging from standard distribution and control panels, to specialized applications in key industries such as traction, energy, maritime, explosive atmospheres, material handling, etc.
--	---

**General**

Style	Feed Through
Color	Gray
Mounting	DIN 3
Series	D 6/8.ADO
Connection Technology	ADO (IDC) System and Screw Clamp
UL Wire Range (AWG)	22-8
Rated IEC Wire Range (Solid) (mm <sup>2</sup> )	2.5
UL/CSA Wire Range for ADO (AWG)	16 - 14
Rated CSA Wire Size (AWG)	14

**Dimension Information**

L x W x H (mm)	56 x 8 x 45
Spacing (mm)	8
L x W x H (in)	2.2 x 0.315 x 1.77
Spacing (inches)	0.315

**Specifications**

UL Current (Amps)	25
-------------------	----

UL Voltage (VAC)	600
Rated UL Wire Size (AWG)	8
IEC Voltage (VAC)	1000
IEC Current (Amps)	24
CSA Voltage (VAC)	600
CSA Current (Amps)	25

#### **Packaging**

T&B Order Multiple	50
T&B Inner Pack	50
Package in Units	750
T&B Sold in UOM	Each
T&B Weight Per UOM	2.5 lbs. per 100

#### **Certifications**

Approvals	UL, IEC, CSA
-----------	--------------

#### **For further technical assistance, please contact us...**

Thomas & Betts - USA  
8155 T&B Blvd.  
Memphis, TN 38125  
[www.tnb.com](http://www.tnb.com)

T&B Technical Support  
MS 3B-50  
8155 T&B Blvd.  
Memphis, TN 38125

Hours: 7AM - 6PM CDT  
Monday-Friday  
Phone: (888) 862-3289  
Fax: (901) 252-1321  
Email: [techsupport@tnb.com](mailto:techsupport@tnb.com)