



**Project:** Guitar Center  
**Location:** Denton, Tx

**C&G Electric, Inc.**  
 4801 W University Drive  
 building 102

**Recessed Service**  
**T&B Catalog Number:**

**UPC Number:** 664-SC  
 78599161882  
**Status:** Active  
**Description:**

2-gang recessed service stamped steel floor box that delivers power, communications and data from standard conduit with no exposed service fittings, maximum capacity-90 cubic inch.

**Features**

- Hinged floor plate is steel reinforced for superior load bearing and provides easy access to devices
- Carpet covering eliminates unsightly service fittings and metal floor plates
- Power cords & low voltage cables run through retractable exit
- Power and communications/data can be disconnected quickly
- Accepts 2 plates, one duplex plate provided.
- Blank partitions available

**Application**

Multiple service floor box that deliver power, communications and data from standard conduit with no exposed service fittings.

**General**

Material	Stamped Steel
Volume (cu.in.)	90
Number of Gangs	2
Conduit Knockouts-Sides	(4)-1 & 1 1/4 concentric & (4)-3/4
Conduit Knockouts-Bottom	None
Before Pour Adjustment (inches)	2 1/2
After Pour Adjustment (inches)	3/4
Wiring Device	Duplex and/or Data/Voice Plate
Box Material	Stamped Steel
Knockouts_IDW	Yes

**Dimension Information**

Dimension A (inches)	3 3/4
Dimension B (inches)	4 11/16
Dimension C (inches)	10 1/4

**Specifications**

3dmodel	Available on Website
Product Specification-DOC	Available on Website
Product Specification-PDF	Available on Website

**Accessories & Components**

Covers &amp; Carpet Plates-664 SC &amp; 664 CI sf\_664scci\_accessories

**Competitor Cross Reference**

Competitive Cross Reference Guide Available on Website

**Packaging**

T&B Inner Pack	1
Package in Units	4
T&B Sold in UOM	Each
T&B Weight Per UOM	363.75 lbs. per 100

**Application Support**

T&B Instruction Sheets	ta02125-tb2
Product Brochure - Brass & Aluminum	Available on Website
Floor Box Covers	
Floor Box Selection Guide	Available on Website
Product Brochure - MopTite Covers	Available on Website

**Notes**

*Note	When using the center side knockouts, catalog number 664-RP must be assembled to the box prior to installing the conduit.
**Note	When ordering a 664 Series box the cover must be ordered separately.

**Certifications**

RoHS Compliance No

**Certifications**File Nbr:  
E 2969**For further technical assistance, please contact us...**Thomas & Betts - USA  
8155 T&B Blvd.  
Memphis, TN 38125  
www.tnb.comT&B Technical Support  
MS 3B-50  
8155 T&B Blvd.  
Memphis, TN 38125Hours: 7AM - 6PM CDT  
Monday-Friday  
Phone: (888) 862-3289  
Fax: (901) 252-1321  
Email:techsupport@tnb.com