



## Wiring Duct T&B Catalog Number:

**UPC Number:**  
**Status:**  
**Description:**

TY6X4WPG6  
78621095690  
Active

Wiring Duct Wide Slot 6 Inch X 4 Inch Rigid PVC Gray

### Features

Wide fingers and slots increase rigidity and enable insertion of bundles. V-Shaped slot lead-in enables easier and faster wire installation. Rounded edges keep hands and wires free of abrasion.

Non-slip cover does not slide easily and resists vibration. Flush cover attaches flush with sidewall for finished look.

Dual score lines are designed to yield clean breakoffs at the base of the slot and the duct. Versatile North American and DIN Standard mounding holes enables same duct for multiple applications.

### General

Style	Wide Slot
Nominal Width (inches)	6
Nominal Height (inches)	4
Material	Rigid PVC
Color	Gray
Adhesive-Backed	No
Mounting Holes	Yes

### Dimension Information

Length (feet)	6
Width (inches)	6.25
Height (inches)	4.46
A (inches)	6.25
B (inches)	4.46
C (inches)	6.25
D (inches)	4.39
E (inches)	0.30
F (inches)	3.63
G (inches)	0.39
H (inches)	0.10
I (inches)	1.00

### Accessories & Components

Cover	TY6CPG6
-------	---------

### Packaging

T&B Order Multiple	30
T&B Inner Pack	6
Package in Units	30
T&B Sold in UOM	Feet
T&B Weight Per UOM	90 lbs. per 100

### Application Support

Product Selector	TD_selector_duct_gray
T&B Sales Drawings	wsd-000180
Technical Information	Available on Website

## Specifications

Available on Website

## Overview

Available on Website

## Wire Fill Calculator

Available on Website

**Notes**

## Options

Catalog Number must be completed by adding suffix G for Gray, W for White, B for Black, I for Intrinsic Blue. To order Adhesive-Backed duct, add suffix A. To order duct without mounting holes, add suffix NM to catalog number. Contact Customer Service for pricing and availability.

Standard lengths are 6 feet.

**Certifications**

## RoHS Compliance

Yes

## Webcat CE\_recognized

Y

**Certifications****For further technical assistance, please contact us...**

Thomas & Betts - USA  
8155 T&B Blvd.  
Memphis, TN 38125  
[www.tnb.com](http://www.tnb.com)

T&B Technical Support  
MS 3B-50  
8155 T&B Blvd.  
Memphis, TN 38125

Hours: 7AM - 6PM CDT  
Monday-Friday  
Phone: (888) 862-3289  
Fax: (901) 252-1321  
Email: [techsupport@tnb.com](mailto:techsupport@tnb.com)