



3" Equipment Rack

Rack Units	Height Inches (mm)	Width Inches (mm)	Rail Depth Inches (mm)	Hole Type	Color	Catalog No.
24	48" (1219)	19" (483)	3" (76)	#12-24 Threaded	Black	HPW48RR19*
24	48" (1219)	23" (584)	3" (76)	#12-24 Threaded	Black	HPW48RR23*
36	68.5" (1676)	19" (483)	3" (76)	#12-24 Threaded	Black	HPW66RR19*
45	84" (2134)	19" (483)	3" (76)	#12-24 Threaded	Black	HPW84RR19*
45	84" (2134)	23" (584)	3" (76)	#12-24 Threaded	Black	HPW84RR23*
48	89.7" (2286)	19" (483)	3" (76)	#12-24 Threaded	Black	HPW90RR19*
48	89.7" (2286)	23" (584)	3" (76)	#12-24 Threaded	Black	HPW90RR23
51	96" (2438)	19" (483)	3" (76)	#12-24 Threaded	Black	HPW96RR19*
51	96" (2438)	23" (584)	3" (76)	#12-24 Threaded	Black	HPW96RR23*

*Add **"ML"** at end of Catalog No. for Mill Finish.



HPW84RR19



CS1976A

3" Equipment Rack with 6" Wide Z-Channels

Rack Units	Height Inches (mm)	Width Inches (mm)	Rail Depth Inches (mm)	Z Depth Inches (mm)	Cover Style	Color	Catalog No.
45	84" (2134)	19" (483)	3" (76)	6" (152)	Hinged	Black	CS1976H
45	84" (2134)	19" (483)	3" (76)	6" (152)	Clip On	Black	CS1976
45	84" (2134)	19" (483)	3" (76)	6" (152)	Clip On	Aluminum	CS1976A

6" Equipment Rack

Rack Units	Height Inches (mm)	Width Inches (mm)	Rail Depth Inches (mm)	Hole Type	Color	Catalog No.
45	84" (2134)	19" (483)	6" (152)	#12-24 Threaded	Black	HPW84RR19D



HPW84RR19D

4-Post, 19" Equipment Rack

Rack Units	Overall Height Inches (mm)	Usable Height Inches (mm)	Overall Width Inches (mm)	Depth Inches (mm)	Hole Type	Color	Catalog No.
45	84" (2134)	79" (2007)	20.2" (513)	24" (610)	#12-24 Threaded	Black	SF841924T
45	84" (2134)	79" (2007)	20.2" (513)	29.23" (742)	#12-24 Threaded	Black	SF841929T
45	84" (2134)	79" (2007)	20.2" (513)	36" (914)	#12-24 Threaded	Black	SF841936T
45	84" (2134)	79" (2007)	20.2" (513)	24" (610)	Square	Black	SF841924
45	84" (2134)	79" (2007)	20.2" (513)	29.23" (742)	Square	Black	SF841929
45	84" (2134)	79" (2007)	20.2" (513)	36" (914)	Square	Black	SF841936



SF841924T