



- Reliable, Efficient Design
- Inline Terminations
- 10/100/1000 BASE-T Assurance
- Eco-Friendly Bulk Packaging Reduces Excess Waste on the Job

**Specifications**

- TIA 568-C.2 Category 5e/6 component compliant
- cULus Listed

Universal Consolidation Blocks and Patch Panels

Ports	Height Inches (mm)	Width Inches (mm)	Depth Inches (mm)	Type	Category	Catalog No.
12	10.00" (254)	3.30" (84)	1.79" (45)	Consolidation Block	5e	NS5E12U
24	1.72" (44)	19.00" (483)	1.24" (31)	Patch Panel	5e	NS5E24U
48	3.47" (88)	19.00" (483)	1.24" (31)	Patch Panel	5e	NS5E48U
12	10.00" (254)	3.30" (84)	1.79" (45)	Consolidation Block	6	NS612U
24	1.72" (44)	19.00" (483)	1.21" (31)	Patch Panel	6	NS624U
48	3.47" (88)	19.00" (483)	1.21" (31)	Patch Panel	6	NS648U

**netSELECT® Category 6, 5e and USOC Jacks**

Color	Modular Snap Fit Cat. 6 Jack (single)	Modular Snap Fit Cat. 6 Jack (25 pack)	Modular Snap Fit Cat. 5e Jack (single)	Modular Snap Fit Cat. 5e Jack (25 pack)	Modular Snap Fit USOC Jack
Almond	NSJ6AL	NSJ6AL25	NSJ5EAL	NSJ5EAL25	NSJUAL
Black	NSJ6BK	NSJ6BK25	NSJ5EBK	NSJ5EBK25	NSJUBK
Blue	NSJ6B	NSJ6B25	NSJ5EB	NSJ5EB25	NSJUB
Gray	NSJ6GY	NSJ6GY25	NSJ5EGY	NSJ5EGY25	NSJUGY
Green	NSJ6GN	NSJ6GN25	NSJ5EGN	NSJ5EGN25	NSJUGN
Ivory	NSJ6I	NSJ6I25	NSJ5EI	NSJ5EI25	NSJUI
Light Almond	NSJ6LA	NSJ6LA25	NSJ5ELA	NSJ5ELA25	NSJULA
Orange	NSJ6OR	NSJ6OR25	NSJ5EOR	NSJ5EOR25	NSJUOR
Red	NSJ6R	NSJ6R25	NSJ5ER	NSJ5ER25	NSJUR
White	NSJ6W	NSJ6W25	NSJ5EW	NSJ5EW25	NSJUW
Yellow	NSJ6Y	NSJ6Y25	NSJ5EY	NSJ5EY25	NSJUY

Note: See page D9 for HC6 and HC5E patch cords.