


Fire-Rated Poke-Throughs for Concrete Floors Hubbell SystemOne Recessed Systems 4 Inch Sub-Plates

The 4 Inch recessed cover is available in a number of durable, yet beautiful finishes to match any décor. The flange height of 0.12 inch is ADA compliant and suitable for use on any floor finish. All covers are UL514A, scrubwater compliant.





Architectural Cover Finishes

Description	Catalog Number
Brushed Aluminum Finish, Single fold under cable egress door.	S1R4CVRALU 
Plated Brushed Brass Finish, Single fold under cable egress door.	S1R4CVRBRS 
Plated Antique Bronze Finish, Single fold under cable egress door.	S1R4CVRBRZ 
Plated Satin Nickel Finish, Single fold under cable egress door.	S1R4CVRNKL 

Note: COVER LOAD RATING: 1,000LBS with 2x safety factor. Load applied through a 3" (76mm) mandrel in center of the cover. Static loads only.

Multi-Service Device Plates

Description	Catalog Number
2X2 Sub-plate with one duplex device opening and two keystone jack openings*.	 S1R4SP2X2DUPLEX
2X2 Sub-plate with one Style Line [®] decorator device opening and two keystone jack openings*.	 S1R4SP2X2STYLE



*Note: *Go to www.hubbell-wiring.com for data jacks and frames.*

*For low light applications (i.e. under tables or podiums) consider using Hubbell's LED illuminated receptacles:
HBL8200ILW 15A, LED or
HBL8300ILW 20A, LED.*








HBL8300ILW

Powder Coated Cover Finishes

Description	Catalog Number
Black Powder Coat Finish, Single fold under cable egress door.	S1R4CVRBLK 
Gray Powder Coat Finish, Single fold under cable egress door.	S1R4CVRGRY 

Note: COVER LOAD RATING: 1,000LBS with 2x safety factor. Load applied through a 3" (76mm) mandrel in center of the cover. Static loads only.

Single-Service Device Plates

Description	Catalog Number
Four single 20A receptacles. Can be wired as single or two circuit with isolated ground capability, 24 inch wire leads.	 S1R4SPQUAD
One 1.60 inch opening for 20 or 30A Twist-Lock [®] receptacle.	 S1R4SPTWIST
One 1.40 inch opening for simplex receptacle.	 S1R4SPSIMPLEX
One duplex device opening for power or datacom* applications.	 S1R4SPDUPLEX
One Style Line [®] decorator device opening for power or datacom* applications.	 S1R4SPSTYLE

*Note: *Go to www.hubbell-wiring.com for data jacks and frames.*