


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

TWIST TIE



T568B WIRING SCHEME

PLUG POSITION:	CABLE WIRE:
1	WHITE/ORANGE
2	ORANGE
3	WHITE/GREEN
4	BLUE
5	WHITE/BLUE
6	GREEN
7	WHITE/BROWN
8	BROWN

NOTES:

1. SEE TABLES FOR AVAILABLE LENGTHS AND COLORS.
2. SEE CURRENT CATALOG FOR VARIOUS APPLICATIONS AND TO INDICATE PACKAGE QUANTITY.
3. SEE CATALOG FOR A COMPLETE LIST OF PARTS APPLICABLE FOR USE WITH THIS PART.

"XX" PART LENGTH TABLE	
PANDUIT P/N	LENGTH
NK6PC3**Y	3 FT
NK6PC5**Y	5 FT
NK6PC7**Y	7 FT
NK6PC9**Y	9 FT
NK6PC10**Y	10 FT
NK6PC14**Y	14 FT
NK6PC20**Y	20 FT
NK6PC1M**Y	1 M
NK6PC2M**Y	2 M
NK6PC3M**Y	3 M
NK6PC4M**Y	4 M
NK6PC5M**Y	5 M

COLOR TABLE	
** CODE	COLOR
NO SUFFIX	WHITE
BU	BLUE
RD	RED
GR	GREEN
YL	YELLOW
VL	VIOLET

XX = LENGTH
** = COLOR

PART NUMBER		NK6PCXX**Y, NK6PCXXM**Y	
TITLE			
NETKEY CATEGORY 6 PATCH CORD			
CUSTOMER DRAWING			
ITEM REVISION NAME		M02479IX/05	
DATASET FILE NAME		M02479IX_DC234/00B	
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN (mm)		MATERIAL:	
.x ± .xxx ± .010 (.3)		DRAWING NUMBER:	
.xx ± .03 (.8) ANGLES ±		02479-234	
THIRD ANGLE PROJECTION		SHT 1 OF 1	
DRAWN BY	DATE	CHK	SCALE
LZ	2-25-06	WJC	NONE
REV	DATE	BY	CHK
1	6/13/14	JSP	REFR
R	2-25-06	LZ	WJC
APR		WJC	
DESCRIPTION		ECN	
A. REVISED DRAWING TITLE BLOCK.		02479-234	
RELEASED TO PRODUCTION		02479-234	

D10100DA/14