THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



PANDUIT P/N	WEIGHT
R2P96	28.5 LB/EACH (13.0 KG/EACH)

NOTES:
1. CAN BE USED WITH ANY INDUSTRY STANDARD 19" COMPONENTS IN ADDITION TO ALL PANDUIT CABLE MANAGEMENT AND PATCH PANEL PRODUCTS.
2. WILL HOLD UP TO 52 SINGLE RACK SPACINGS.
3. EIA SPACING ON RACK: I.E., REF. HOLE SPACING ON UPRIGHT CHANNELS: .625, .625, .500, .625, .625, .500, ETC.
4. ASSEMBLY IS REQUIRED.
5. RACK PART THICKNESSES:
   - UPRIGHT CHANNEL: WEB; .14 ±.03
     FLANGE; .19 ±.03
   - TOP BRACKET: .19 ±.03
   - BASE BRACKET: .25 ±.03
6. DIMENSIONS IN PARENTHESES ARE IN METRIC.
7. ALL ASSEMBLY HARDWARE INCLUDED:
   -(12) 3/8-16 X 1" BLACK HEX HEAD CAP SCREW
   -(24) 3/8" PAINT PIERCING GROUNDING WASHER
   -(1) TUBE OF ANTI-OXIDIZING PASTE
   -(12) 3/8-16 BLACK HEX NUTS
   -(24) 12-24 X .5" SLOTTED PAN HEAD STEEL SCREWS
8. LOAD RATING - 1000 LBS
9. RU SPACING NUMBERS ARE CLEARLY PRINTED ON MOUNTING RAILS. RU NUMBERING IS BOTTOM-UP, WITH RU #1 AT BOTTOM AND RU #45 AT TOP.

REV	DATE	BY	CHK	APR	DESCRIPTION	ECN
01A	11-14-13	BAME	PM	CMK	UPDATED VIEWS	09V064AD-DC
00A	5-27-10	BAME	DPN	CMK	DRAWING RELEASED	09V064AD-DC

TITLE

8 FOOT CABLE MANAGEMENT RACK (R2P96)

CUSTOMER DRAWING

ITEM REVISION NAME: 09V064AD/01

DATASET FILE NAME: 09V064AD_DC/01A

UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm]

.X ± .XXX ±

.XX ± ANGLES ±

THIRD ANGLE PROJECTION

MATERIAL: ALUMINUM

DRAWING NUMBER: 09V064AD-DC

DRAWN BY	DATE	CHK	SCALE	SIZE
BAME	5-27-10	DPN	NONE	A

SHT 1 OF 2

D10100DA/16

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.





REV	DATE	BY	CHK	APR	DESCRIPTION	ECN
01A	11-14-13	BAME	PM	CMK	SEE SHEET 1 OF 2 FOR REVISIONS	09V064AD-DC
00A	5-27-10	BAME	DPN	CMK	SEE SHEET 1 OF 2 FOR REVISIONS	09V064AD-DC

TITLE

8 FOOT CABLE MANAGEMENT RACK (R2P96)

CUSTOMER DRAWING

ITEM REVISION NAME: 09V064AD/01

DATASET FILE NAME: 09V064AD_DC/01A

PANDUIT

UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm]

.X ± .XXX ±

.XX ± ANGLES ±

THIRD ANGLE PROJECTION

MATERIAL: ALUMINUM

DRAWING NUMBER: 09V064AD-DC

DRAWN BY	DATE	CHK	SCALE	SHT 2 OF 2	SIZE
BAME	5-27-10	DPN	NONE		A