



Project: edwards
Location: nf ny

Wiring Duct
T&B Catalog Number:

TY15X15NPW6

UPC Number:

78621097032

Status:

Active

Description:



Wiring Duct Narrow Slot 1-1/2 Inch X 1-1/2 Inch Rigid PVC White

Features

Smaller, higher number of fingers for more concise harnessing. V-Shaped slot lead-in enables easier and faster wire installation. Rounded edges keep hands and wires free of abrasion.

Non-slip cover does not slide easily and resists vibration. Flush cover attaches flush with sidewall for finished look.

Dual score lines are designed to yield clean breakoffs at the base of the slot and the duct. Versatile North American and DIN Standard mounding holes enable same duct for multiple applications.



General

| | |
|-------------------------|-------------|
| Style | Narrow Slot |
| Nominal Width (inches) | 1.5 |
| Nominal Height (inches) | 1.5 |
| Material | Rigid PVC |
| Color | White |
| Adhesive-Backed | No |
| Mounting Holes | Yes |

Dimension Information

| | |
|-----------------|------|
| Length (feet) | 6 |
| Width (inches) | 1.75 |
| Height (inches) | 1.60 |
| A (inches) | 1.75 |
| B (inches) | 1.60 |
| C (inches) | 1.75 |
| D (inches) | 1.03 |
| E (inches) | 0.20 |
| F (inches) | 0.52 |
| G (inches) | 0.26 |
| H (inches) | 0.10 |
| I (inches) | 0.50 |

Accessories & Components

| | |
|-------|----------|
| Cover | TY15CPW6 |
|-------|----------|

Packaging

| | |
|--------------------|------|
| T&B Order Multiple | 120 |
| T&B Inner Pack | 6 |
| Package in Units | 120 |
| T&B Sold in UOM | Feet |

T&B Weight Per UOM 18.75 lbs. per 100

Application Support

| | |
|-----------------------|------------------------|
| Product Selector | TD_selector_duct_white |
| T&B Sales Drawings | wsd-000181 |
| Technical Information | Available on Website |
| Specifications | Available on Website |
| Overview | Available on Website |
| Wire Fill Calculator | Available on Website |

Notes

| | |
|---------|--|
| Options | Catalog Number must be completed by adding suffix G for Gray, W for White, B for Black, I for Intrinsic Blue. To order Adhesive-Backed duct, add suffix A. To order duct without mounting holes, add suffix NM to catalog number. Contact Customer Service for pricing and availability. Standard lengths are 6 feet. |
|---------|--|

Certifications

| | |
|----------------------|-----|
| RoHS Compliance | Yes |
| Webcat CE_recognized | Y |

Certifications

For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

T&B Technical Support
MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email:techsupport@tnb.com