



Project: PEAK 10
Location: RALEIGH, NC
MILLER ELEC

Standard
T&B Catalog Number:

TY526M
 78621082549
 Active

UPC Number:
Status:
Description:

Cable Tie 30lb 11" Natural Nylon with Stainless Steel Locking Device Distributor Pack

Features

Low profile head is designed to prevent snags on uneven surfaces and easier to pull through bulk-heads. Non-magnetic stainless steel locking device insures both maximum strength and the right tightness every time.

Because there are no notches, Ty-Rap ties provide an infinite number of locking positions while fastening the tie at the precise bundle diameter needed.

The No-Slip Tail provides easy grip during tensioning. Ty-Rap ties feature a unique friction surface designed to reduce slippage during installation.

Smooth, notchless body reduces stress concentration points under tension, making the tie stronger and lower profile than notched body ties. Ribbed and Stippled body grips the bundle and prevents slippage. Rounded edges protect insulation, preventing sharp edges from damaging cables.

General

| | |
|----------|-----------|
| Material | Nylon 6.6 |
| Color | Natural |

Dimension Information

| | |
|------------------------------------|------|
| Nominal Length (inches) | 11 |
| Length (inches) | 11.1 |
| Width (inches) | .140 |
| Max. Wire Bundle Diameter (inches) | 3 |

Specifications

| | |
|---------------------|----------------|
| Temperature Rating | -40°F to 185°F |
| Flammability Rating | UL 94 V-2 |

Tooling

| | |
|-------------------|---------------|
| Application Tools | ERG50, WT1-TB |
|-------------------|---------------|

Packaging

| | |
|--------------------|---------|
| T&B Order Multiple | 100 |
| T&B Inner Pack | 100 |
| Package in Units | 500 |
| Package Type | Regular |
| T&B Sold in UOM | Each |

| | |
|--------------------|--------------------|
| T&B Weight Per UOM | 3.75 lbs. per 1000 |
|--------------------|--------------------|

Application Support

| | |
|--------------------------|----------------------|
| Material Selection Guide | Available on Website |
|--------------------------|----------------------|

| | |
|------------------|----------------------|
| Available Colors | Available on Website |
|------------------|----------------------|

Certifications

| | |
|-----------------|-----|
| RoHS Compliance | Yes |
|-----------------|-----|

For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

T&B Technical Support
MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email: techsupport@tnb.com