



Compatible with Hubbell Labeling System, see page U7.



- Designed to Flush Mount with Box Eliminator
- Adjustable Leveling Feature
- ANSI/TIA-606-B Compliant



Specifications



- Fits all Hubbell keystone connections (AV, data and fiber)
- Available in single and double gang
- All IFP plates are supplied with paper labels, clear screw covers, and color matched screw covers
- Secure; must remove plate to access connectivity

IFP Faceplates, Single Gang


Ports	1-Port	2-Port	3-Port	4-Port	6-Port
Unit of Measure	1 per bag	1 per bag	1 per bag	1 per bag	1 per bag
Catalog No.	IFP11xx	IFP12xx	IFP13xx	IFP14xx	IFP16xx



IFP11OW IFP12OW IFP13OW

IFP Faceplates, Double Gang

Ports	6-Port	9-Port	12-Port
Unit of Measure	1 per bag	1 per bag	1 per bag
Catalog No.	IFP26xx	IFP29xx	IFP212xx



IFP26OW IFP212OW

NS Faceplates, Single Gang, Without Label Fields

Ports	1-Port	2-Port	3-Port	4-Port	6-Port
Unit of Measure	1 per bag	1 per bag	1 per bag	1 per bag	1 per bag
Catalog No.	NSP11xx	NSP12xx	NSP13xx	NSP14xx	NSP16xx



NSP11I NSP13I NSP26I

NS Faceplates, Single Gang, Midsize, Without Label Fields

Ports	1-Port	2-Port	3-Port	4-Port	6-Port
Unit of Measure	1 per bag	1 per bag	1 per bag	1 per bag	1 per bag
Catalog No.	NSP101xx	NSP102xx	NSP103xx	NSP104xx	NSP106xx

NS Faceplates, Double Gang, Without Label Fields

Ports	4-Port	6-Port
Unit of Measure	1 per bag	1 per bag
Catalog No.	NSP24xx	NSP26xx



NP13I

Blank Wallplates

	Standard				Midsize	
Gangs	1-Gang	2-Gang	3-Gang	4-Gang	1-Gang	2-Gang
Catalog No.	NP13xx	NP23xx	NP33xx	NP43xx	NPJ13xx	NPJ23xx

Angled Faceplates, 4-Port, Single Gang

Color	Electric Ivory	Gray	Office White	White
Catalog No.	AFP14EI	AFP14G	AFP14	AFP14W



AFP14

xx = Color: **AL** (Almond), **BK** (Black), **EI** (Electric Ivory), **GY** (Gray), **LA** (Light Almond), **OW** (Office White), and **W** (White). For all NS and NP series plates, use **I** for Ivory. Light Almond is the same color as Office White. Almond is not available in single gang. See color chart on page V30.