


Middle Atlantic Products

EXCEPTIONAL SUPPORT & PROTECTION™

Rackmount LCD, Keyboard and Touchpad


EIA/TIA Compliant

Single Rackspace LCD Monitor and Keyboard with Integrated Touchpad

Features

- Space saving design occupies a single rackspace
- Easy to read bright active matrix LCD display
- LCD can be in open position for system monitoring while keyboard is in the closed position
- Comes standard with installed keylock for security
- Standard 105 key PS/2 keyboard with touchpad
- 1280 x 1024 screen resolution
- Available with KVM switch
- 6' connector cable included
- No hassle 1 year limited warranty



RM-KB-LCD

Architects' and Engineers' Specifications

EIA compliant 19" rackmount LCD monitor, keyboard with integrated touchpad shall be Middle Atlantic Products part # RM-KB-LCD17 __ and shall occupy 1 rackspace (refer to chart). Overall dimensions shall be 1.75" H x 19" W x 22" D. RM-KB-LCD17 __ shall have a rail to rail mounting range of 18.25" to 27.75". The chassis shall be constructed of 16-gauge and 18-gauge steel. Keyboard shall have a standard 105 key PS/2 keyboard with integrated touchpad. LCD display size shall be 17" diagonal with a resolution of 1280 x 1024. Screen shall have a typical contrast ratio of 350:1. Power source shall be 50/60 Hz, 120 - 240V AC with a power consumption of 25 watts. Included power cord shall be provided with a NEMA 5-15P plug. Keyboard with LCD display shall have an operating range of 32°F - 122°F. RM-KB-LCD17 __ shall include KVM switch with __ ports (refer to chart). Keyboard with LCD display shall comply with part 15 of the FCC rules and comply with CE regulation EN 55 022:Class B. Finished in a black powder coat. Rackmount LCD monitor and keyboard with integrated touchpad shall be GREENGUARD Indoor Air Quality Certified for Children and Schools. Rackmount LCD monitor and keyboard with integrated touchpad shall be RoHS EU Directive 2002/95/EC compliant. Rackmount LCD monitor and keyboard with integrated touchpad shall be manufactured by an ISO 9001 registered company. Rackmount LCD monitor and keyboard with integrated touchpad shall be warranted to be free from defects in parts or materials under normal use and conditions for a period of 1 year.

OPTIONS

- PS/2 and USB cables shall be PS/2USB-4C, 4 qty.

CUSTOMIZABLE SPECIFICATION CLIPS AVAILABLE AT MIDDLEATLANTIC.COM

Rackmount LCD Keyboard and Touchpad basic dimensions


All dimensions in inches unless otherwise noted [All dimensions in brackets are millimeters]




REAR VIEW of RM-KB-LCD17






REAR VIEW of RM-KB-LCD17X8KVM



REAR VIEW of RM-KB-LCD17X16KVM



LCD screen can be in open position for system monitoring while keyboard is in the closed position



Part #	Quantity of KVM switch	Quantity of KVM cables included
RM-KB-LCD17	1	1
RM-KB-LCD17X8KVM	8	4
RM-KB-LCD17X16KVM	16	8

