

**SPEEDGAIN® Category 5e is designed to support reliable Gigabit Ethernet performance. The SPEEDGAIN system is available in a variety of colors, lengths and configurations for multiple applications.**



### SPEEDGAIN® Category 5e Jacks

Unit of Measure	Catalog No.
1 per bag	<b>HXJ5E<sub>xx</sub>*</b>
25 per bag	<b>HXJ5E<sub>xx</sub>25</b>

**xx** = Color: **AL** (Almond), **B** (Blue), **BK** (Black), **BN** (Brown), **EI** (Electric Ivory), **GL** (Gold), **GY** (Gray), **GN** (Green), **LA** (Light Almond), **OW** (Office White), **OR** (Orange), **P** (Purple), **R** (Red), **TI** (Telco Ivory), **W** (White), and **Y** (Yellow). Light Almond is the same color as Office White. See color chart on page V30. \*EI and OR available in 25-pack only.



### SPEEDGAIN® Category 5e, Universal Patch Panels

Format	Width (mm)	Color	Catalog No.
Standard	19" (483)	Black	<b>P5E<sub>xx</sub>U</b>
Standard	19" (483)	White	<b>P5E<sub>xx</sub>UW</b>
Angled	19" (483)	Black	<b>P5E<sub>xx</sub>AU</b>

**xx** = Port Size: **24** (24 ports); **48** (48 ports).

See page E8 for additional colors and catalog numbers.



### SPEEDGAIN® GbE Ethernet, Patch Panels

Format	Width (mm)	Color	24 Port Catalog No.	48 Port Catalog No.
Standard	19" (483)	Black	<b>PG24</b>	<b>PG48</b>



### SPEEDGAIN® Category 5e, Universal Patch Cords

Unit of Measure	Catalog No.
1 patch cord	<b>HC5E<sub>xyy</sub></b>

**xx** = Color: **B** (Blue), **BK** (Black), **GY** (Gray), **GN** (Green), **OR** (Orange), **P** (Purple), **R** (Red), **W** (White), and **Y** (Yellow).

**yy** = Standard Length: **01** (1'), **03** (3'), **05** (5'), **07** (7'), **10** (10'), **15** (15'), **20** (20').

Made-to-order lengths are available from 25ft to 100ft in 5ft increments.



### SPEEDGAIN® Category 5e, UTP Cable, 4-Pair

	REELEX® Plenum Box	REELEX® Riser Box
Blue	<b>C5EPRPB</b>	<b>C5EPRRB</b>
Gray	<b>C5EPRPGY</b>	<b>C5EPRRGY</b>
White	<b>C5EPRPW</b>	<b>C5EPRRW</b>
Yellow	<b>C5EPRPY</b>	<b>C5EPRRY</b>

Note: All category rated cable is packaged in 1000 foot quantities. See section F for additional cable requirements. REELEX® is licensed and patented by Windings Inc.



### SPEEDGAIN® Category 5e, Trunk Cable Assemblies

BIDnet offers a "Green" approach to cabling by providing the exact lengths and number of connections, eliminating unwanted cable waste.

- Simplifies installation time by 75%
- Reduces initial installation cost by 30%
- 100% factory tested and assembled
- Mission Critical 25-Year Warranty

Note: Contact your local distributor or Hubbell's customer service for additional information on BIDnet Pre-Terminated Copper Trunk Assemblies.



### SPEEDGAIN® Category 5e, Field Termination Kits

Description	Catalog No.
50-pair termination kit with 4-pair blocks	<b>110BLK50FTK4</b>
100-pair termination kit with 4-pair blocks	<b>110BLK100FTK4</b>
300-pair termination kit with 4-pair blocks	<b>110BLK300FTK4</b>

Note: See page E16 for more information on 4- and 5-pair Category 5e blocks.

