



WLI-UC-GNHP

## High-Gain Compact USB 2.0 Adapter

AirStation HighPower N150 Compact Wireless USB 2.0 Adapter offers a portable high-speed wireless connectivity to your Windows laptop or desktop through an available USB port. With faster wireless data rates and more coverage than legacy 802.11 products, WLI-UC-GNHP provides better performance than most PCs' internal wireless card. This wireless client offers sufficient bandwidth and range to stream video, voice, and music. Support for the AirStation One-Touch Secure System™ (AOSS™) allows you to set up a high-speed, secure wireless network within minutes.



Wirelessly connect to the internet:



- Send Email
- Download Music
- Surf Web and more



### USB Port

Add high-speed wireless connectivity through an available USB port on your laptop or desktop



### HighPower

Adjustable high gain antenna for greater range and speed

## Features and Benefits

### High-Gain Antenna

Omni-directional antenna for extended range and higher transfer speed

### Slim Design for Portability and Convenience

Great for wireless hotspots and on the go

### Sleek Round Form Factor

Perfect for small laptops and netbooks

### AOSS (AirStation One-Touch Secure System)

Connect other AOSS devices with the push of a button

### Wide Range of Wireless Security Support

WPA2, WPA-PSK (TKIP, AES), and WEP (128/64bit)

### USB 2.0 Support

Easy wireless access using your laptop's or PC's USB port

### Connect to All Wireless Networks

802.11n, 802.11g and 802.11b


### Easy Setup

Simple to install and use - even for the novice user


### Adjustable Antenna

Eliminate dead spots by fine-tuning your antenna positioning

## Easy & Secure Wireless Setup with AOSS



## Adjustable High Gain Antenna for Optimized Speed and Range



## WLI-UC-GNHP



### SPECIFICATIONS

#### Wireless LAN Interface

Access Mode	Infrastructure Mode
Antenna (Tx x Rx)	1 x 1
Interface	USB 2.0
Interface Voltage	5V
Wireless Security	WPA2, WPA-PSK (AES, TKIP), 128/64-bit WEP

#### Other

Dimensions (WxHxD in.)	4.3 x 0.6 x 0.6
OS Support	Windows® 7 (32-bit/64-bit), Windows Vista® (32-bit), Windows® XP, Windows® 2000

## About Buffalo

[www.buffalotech.com](http://www.buffalotech.com)

Buffalo Technology (USA), Inc., based in Austin, Texas, is a leading global provider of award-winning networking, storage and multimedia solutions for the home and small business environments as well as for system builders and integrators. With almost three decades of networking and computer peripheral experience, Buffalo has proven its commitment to delivering innovative solutions that have put the company at the forefront of infrastructure technology.