


APC Back-UPS Pro 500



Battery backup for home networking and home computer equipment

The Back-UPS Pro 500 provides abundant battery backup power and surge protection for your home networking equipment, specifically designed to keep you connected to the Internet during power outages. Unique benefits include user configurable outlets, remote network management via a web browser, and a lithium-ion battery that provides twice the service life of a typical UPS. Providing maximum availability and peace of mind, the Back-UPS Pro 500 is the perfect unit to protect your home network, notebook computer, or business' productivity from the constant threat of power problems and lost data.



Product Features:

- 1 4 Power Protection outlets**
Back up and protect your hardware and data during power outages, surges and spikes.
- 2 Smart Outlets**
Can be remotely managed and individually configured to provide battery backup and/or surge protection. Monitor and control energy usage to optimize power efficiency, reduce energy costs and minimize your environmental impact.
- 3 Lithium-ion battery**
Provides twice the service life of a typical lead acid battery and is small, light and environmentally friendly.
- 4 Remote network manageability**
Monitor your power status and manage your UPS via a web browser.
- 5 Watchdog**
Keeps you connected to the Internet by detecting the loss of network connectivity and automatically rebooting network devices.
- 6 Email notification**
Receive an email notification when there is a power disturbance.
- 7 Telephone dataline surge protection**
Provides protection of connected equipment from power surges traveling on telephone lines.
- 8 Sleek Design**
Slim, modern design can be upright, flat, or wall-mounted to comfortably fit any electronics set-up and complement home décor.

Back-UPS Pro 500 Specifications

Model Number	BG500
Output	
Output Capacity	500VA /300 Watts
Output Voltage / Freq. (utility)	120V, 50/60Hz auto sensing
Output Voltage / Freq. (battery)	120V, 50/60Hz auto sensing
Output Connections	4 total outlets: 2 battery backup & surge / 2 battery optional & surge
Waveform Type	Quasi-sine Wave
Input	
Input Voltage / Frequency	120V 50/60Hz auto sensing
Input Connection	6 foot power cord
Surge Protection	
AC Power Surge Protection	All outlets
Data Line Surge Protection	Telephone (RJ-11)
Physical	
Unit Dimensions (H x W x D)	2.13" x11.42" x7.52"
Unit Weight	4.84 lbs
Shipping Dims. (H x W x D)	3.82"x11.16"x14.57"
Shipping Weight	6.38 lbs
Color	Black
UPC Code	731304299585
Battery	
Battery Type	Maintenance-free, Lithium Ion
Management	
Alarms	Visual (LED) and audible alarms
Safety	
Regulatory Approvals	California (CEC) Battery Charger, cTUVus, ENERGY STAR (USA), FCC Part 15 Class B, FCC Part 68, UL 1778
Runtime	
25 / 40 / 180 Watts	44 / 29 / 6.5 minutes
Warranty	
Warranty	Three-year factory repair or replace
Equipment Protection Policy	\$150,000 Lifetime connected equipment protection policy

APC by Schneider Electric

132 Fairgrounds Rd
West Kingston, RI 02892
Tel: 401-789-5735
800-800-4272
Fax: 401-789-3710
www.apc.com

