

APC External Battery Pack

Extended battery backup time for the Back-UPS Pro 1500 VA models

The BR24BPG is an external battery pack that plugs into the rear panel of 1500VA Back-UPS Pro models. Connecting the BR24BP battery pack will approximately triple the normal amount of runtime provided by your standard Back-UPS Pro unit.



Product Features:

- 1 Four 9Ah batteries dramatically extend the runtime of your 1500VA Back-UPS Pro unit. (1500VA Back-UPS Pro models contain two 9Ah batteries standard.)
- 2 Consistent styling with APC's Back-UPS Pro models.
- 3 Recharges automatically via the Back-UPS Pro's internal charger.
- 4 Heavy duty connector plugs securely into the rear panel of the 1500VA Back-UPS Pro.
- 5 Vented, high strength, flame retardant housing provides durability and efficient thermal management.
- 6 2 year warranty



Rear of BR1500G
(sold separately)

BR24BPG Specifications

Model Number	BR24BPG
Output	
Output Voltage	12Vdc
Output Connection	proprietary, non-reversible connector
Input	
Input Voltage	12Vdc
Physical	
Unit Dimensions (H x W x D)	11.9 x 4.4 x 15.0" (30.1 x 11.2 x 38.2 cm)
Unit Weight	29.5 lbs (13.4 kg)
Shipping Dimensions (H x W x D)	15.0 x 9.0 x 19.0" (381 x 229 x 483 cm)
Shipping Weight	32.1 lbs (14.6 kg)
Color	Black
UPC Code	731304268789
Compatibility	
The BR24GBP and BR24BP are interchangeable, but their styling and color are significantly different.	<p>Use BR24GBP with: BR1500G (NAM), BR1500G-BR (Brazil), BR1500G-FR (France), BR1500G-IN (India), BR1500-AR (Argentina), BR1500G-CN (China), BR1500G-GR (Germany), BR1500GI (Worldwide)</p> <p>Use BR24BP with: BR1500, BX1500 (NAM), BR1500I (Worldwide)</p>
Battery	
Expected Life	4 - 6 yrs
Battery Type	Maintenance-free, sealed lead-acid battery, leakproof

Approx Runtimes: 1500VA Back-UPS Pro with and without the BR24BPG External Battery Pack

LOAD: <u>Watts / VA</u>	<u>Runtime without</u> <u>the BR24BPG</u>	<u>Runtime with</u> <u>the BR24BPG</u>
50 / 80	157 min	446 min
100 / 160	80 min	232 min
200 / 320	37 min	110 min
300 / 480	22 min	69 min
400 / 640	14 min	49 min
500 / 800	10 min	37 min
600 / 960	7 min	29 min
700 / 1120	5 min	24 min
800 / 1333	4 min	20 min

For more information on runtimes, go to: www.apc.com/sizing

APC by Schneider Electric
 132 Fairgrounds Rd
 West Kingston, RI 02892
 Tel: 800-800-4272
www.apc.com

APC
 by Schneider Electric