



Altronix®

HubSat®8Di Passive UTP Transceiver Hub with Integral Camera Power

Rev. DSHubSat8Di_10162014



HubSat8Di



Overview

HubSat8Di Passive UTP Transceiver Hub with Integral Camera Power transmits UTP video, RS422/RS485 data and power over a single CAT-5 or higher structured cable. Unit provides 8 camera channels in a wall mount enclosure. Video transmission range is up to 750 ft. max. per channel. Units are compatible with AC and/or DC fixed or PTZ cameras when utilizing Altronix HubWayAv or HubWayDv Video Balun/Combiners.

In addition, the unit features 24VAC or 28VAC PTC protected electronically isolated outputs and surge suppression. Optionally, the HubSat8D can be used as an accessory module to transmit video from up to 8 cameras over two (2) separate CAT-5 or higher structured cables back to the HubWay, HubWayLD or HubWayLDH Passive and Active UTP Transceiver Hubs. HubSat8Di powers these cameras locally to eliminate the possibility of voltage drop associated with long cable runs.

Specifications

Input:

- 115VAC 50/60Hz, 1.5 amp.
- Primary fuse (internal) is rated at 3.5 amp/250V.

Output:

- Individually selectable 24VAC or 28VAC power outputs with OFF position.
- Unit provides up to 1 amp max. per channel not to exceed a total of 8 amp (100VA) maximum current.
- Class 2 Rated power-limited outputs.
- PTC protected outputs are rated @ 1 amp per channel.
- Surge suppression.

Video:

- Eight (8) channels of video over twisted pair up to a distance of 750 ft. (228.6m) per channel.
- Eight (8) 75 ohm video outputs.

Data:

- RS422/RS485 data inputs.

Visual Indicators:

- Eight (8) individual power LED indicators.

Accessories:

- Video Balun/Combiners:
 - HubWayAv - for use with 24VAC cameras.
 - HubWayAv2 - for use with 24VAC cameras.
 - HubWayDv - for use with 12VDC cameras.
 - HubWayDvi - for use with 12VDC cameras without isolation.

Mechanical:

- Enclosure Dimensions (H x W x D approx.): 13.5" x 13" x 3.25" (342.9mm x 330.2mm x 82.55mm)
- Product weight: 13.7 lbs. (6.21kg).
- Shipping weight: 14.6 lbs. (6.62kg).

Agency Approvals



UL Listed for Commercial CCTV Equipment (UL 2044).




CUL Listed - CSA Standard C22.2 No.1-04, Audio, Video and Similar Equipment.

Video Balun/Combiners


HubWayAv - Video Balun/Combiner

compatible with all HubWay UTP Hubs for AC fixed cameras or PTZs.




HubWayAv2 - Slim-line Video Balun/Combiner

compatible with all HubWay UTP Hubs for AC fixed cameras or PTZs.




HubWayDv - Video Balun/Combiner

compatible with all HubWay UTP Hubs for DC fixed cameras or PTZs.



HubWayDvi - Video Balun/Combiner

built-in isolation. Compatible with all HubWay UTP Hubs for DC fixed cameras or PTZs. With or without internal isolation.



Enclosure Dimensions (H x W x D approximate):

13.5" x 13" x 3.25" (342.9mm x 330.2mm x 82.55mm)

