




[On Line Catalog](#)

|                                                                                                                                                                                                                                                             |                                   |                             |           |                                                                                                |
|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|-----------------------------------|-----------------------------|-----------|------------------------------------------------------------------------------------------------|
| <br><br> | <b>BURNDY Catalog Number</b>      | YAV10L36                    |           |                                                                                                |
|                                                                                                                                                                                                                                                             | <b>UPC Number</b>                 | 781810025161                |           |                                                                                                |
|                                                                                                                                                                                                                                                             | <b>Description</b>                | 12-10 HVYDTY RING 8-10 S    |           |                                                                                                |
|                                                                                                                                                                                                                                                             | <b>Status</b>                     | Active                      |           |                                                                                                |
|                                                                                                                                                                                                                                                             | <b>Web Use</b>                    | BURNDY Product Line         |           |                                                                                                |
|                                                                                                                                                                                                                                                             | <b>Dimensional</b>                | Length (in)                 | 0.83      |                                                                                                |
|                                                                                                                                                                                                                                                             |                                   | Tongue Type                 | Ring      |                                                                                                |
|                                                                                                                                                                                                                                                             |                                   | Stud Size (in)              | #8        |                                                                                                |
|                                                                                                                                                                                                                                                             |                                   | Pad Width (in)              | 0.29      |                                                                                                |
|                                                                                                                                                                                                                                                             | <b>General</b>                    | Product Description         |           | Copper Terminal, Ring Tongue w/ Inspection Hole, Wire Range 12-10 AWG, #8-#10 Stud, Tin Plated |
|                                                                                                                                                                                                                                                             |                                   | <b>Conductor(s)</b>         |           | N/A                                                                                            |
|                                                                                                                                                                                                                                                             | <b>Physical</b>                   | Aircraft Cable Size (Range) |           | 12-10                                                                                          |
|                                                                                                                                                                                                                                                             |                                   | Copper Solid Size (Range)   |           | N/A                                                                                            |
|                                                                                                                                                                                                                                                             |                                   | Navy Cable Size (Range)     |           | 12-10                                                                                          |
|                                                                                                                                                                                                                                                             |                                   | Copper Stranded (Range)     |           |                                                                                                |
|                                                                                                                                                                                                                                                             | <b>Approvals / Certifications</b> | Type of Plating             |           | Tin - Electro Plated                                                                           |
|                                                                                                                                                                                                                                                             |                                   | Connector Type              |           | Terminal - Ring                                                                                |
|                                                                                                                                                                                                                                                             |                                   | Plated (Yes or No)          |           | Y                                                                                              |
|                                                                                                                                                                                                                                                             |                                   | UL Listed                   |           | Y                                                                                              |
| <b>Documentation</b>                                                                                                                                                                                                                                        | CSA Certified                     |                             | Y         |                                                                                                |
|                                                                                                                                                                                                                                                             | ROHS Compatible                   |                             | Compliant |                                                                                                |
|                                                                                                                                                                                                                                                             | UL Recognized                     |                             | N         |                                                                                                |
|                                                                                                                                                                                                                                                             | CULUS                             |                             | N         |                                                                                                |
|                                                                                                                                                                                                                                                             | Industry Standards                |                             | UL467     |                                                                                                |

For further technical assistance, please contact us

**BURNDY LLC - USA**  
47, industrial Park Drive  
Manchester NH03109

**BURNDY Technical Servcies**  
47, industrial Park Drive  
Manchester NH03109

Hours: 8.00 AM - 5.00 PM  
Monday - Friday  
Phone: 000-346-4175