

External 72V 2U Rack/Tower Battery Pack for select Tripp Lite UPS Systems (BP72V15-2U)

MODEL NUMBER: **BP72V15-2U**



Description

BP72V15-2U rack/tower external battery pack offers extended battery runtime when used in conjunction with expandable 72V Tripp Lite rackmount and tower UPS systems. Includes heavy gauge cabling with high current DC connector for safe, simple installation. Included mounting accessories support 2U rackmount installation in 4 post racks. Options for 2-point front-rail mounting, 2 post center-mounting, wallmount and upright tower installation available.

Compatible with these UPS Systems - SMART3000MOD2U, SU3000RTXL2U, SU3000RTXL3U, SU3000RTXL3UHV, SU3000RTXLCD2U, SU3000RTXLCD3U, SU3000RTXR3U, SU3000RTXR3UHW, SU3000XL, SU3000XLCD, SUI3000RTXL2U, SUI3000RTXL3U and other Tripp Lite UPS systems that specify the use of this battery pack.

Features

- Offers extended-run UPS operation when used in conjunction with compatible 72V DC Tripp Lite UPS systems
- Includes heavy gauge cabling with high current DC connectors for simple installation
- Included mounting brackets support rackmount installation in 4 post racks using only 2 rack spaces (2U)
- UPDHDEARKIT option supports 2 point front-rail rackmount installation without rear supports
- 2POSTRMKITWM option supports balanced 2 point center-mounting in 2 post equipment racks
- 2POSTRMKITWM option also enables wallmount installation
- 2-9USTAND option enables upright tower placement
- NOTE: LIMIT OF 1 BP72V15-2U PER UPS, SEE BP72V18-2US or BP72V28RT-3U FOR MULTI-PACK COMPATIBILITY

Specifications

General Info	
RoHS	Y

Highlights

- Extends the runtime of compatible 72V Tripp Lite UPS Systems
- Supports 2U rackmount installation; 4 post installation accessories included
- Options for 2 post rackmount, tower and wallmount installation available

Applications

Ideal means of lengthening the battery runtime provided by compatible Tripp Lite UPS systems

Package Includes

- BP72V15-2U external battery pack with attached DC cabling
- 4 post compatible mounting hardware
- Owner's manual



BATTERY	
DC System Voltage (VDC)	72
UPS Connection	DC connector
Typical Battery Lifespan	4-6 years typical (North America)
PHYSICAL	
Installation Form Factors Supported with Included Accessories	4 post 19 inch rackmount
Installation Form Factors Supported with Optional Accessories	2 post rackmount (2POSTRMKITWM); Wallmount (2POSTRMKITWM); Tower (2-9USTAND); 2-4 post front rail rackmount (UPSHDEARKIT)
Shipping Dimensions (hwd / in.)	10 x 28.5 x 26.5
Shipping Dimensions (hwd / cm)	25.4 x 72.4 x 67.3
Shipping Weight (lbs.)	120
Shipping Weight (kg)	54.5
Unit Dimensions (hwd / in.)	3.5 x 17.5 x 20.75
Unit Dimensions (hwd / cm)	8.9 x 52.7 x 52.7
Unit Weight (lbs.)	72.4
Unit Weight (kg)	32.9
Material of Construction	Steel
WARRANTY	
Product Warranty Period (U.S. & Canada)	2-year limited warranty
Product Warranty Period (International)	1-year limited warranty
Product Warranty Period (Mexico)	1-year limited warranty
Product Warranty Period (Puerto Rico)	1-year limited warranty

© 2015 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.