

## Component Video with Stereo Audio over Cat5/Cat6 Extender, Wallplate Remote Receiver

MODEL NUMBER: **B136-100-WP-1**



### Description

The B136-100-WP-1 is a remote extender wallplate for the B136-004, 4-Port Component Video + Audio Extender/Splitter. A 1080i (60Hz) Component Video and Stereo Audio signal can be extended up to 300 ft. when using 24Awg, Solid Wire UTP cable (Tripp Lite N022-01K-GY or N222-01K-GY); or, up to 400 ft. when using Zero-Skew UTP cable (Tripp Lite P524-01K). A 480p (60Hz) Component Video and Stereo Audio signal can be extended up to 500 ft. when using 24Awg, Solid Wire UTP cable (Tripp Lite N022-01K-GY or N222-01K-GY); or, up to 700 ft. when using Zero-Skew UTP cable (Tripp Lite P524-01K). No external power required.

### Features

- Remote extender wallplate for the B136-004 4-port Extender/Splitter
- RJ45 Jack rear connector
- A 1080i (60Hz) Component Video and Stereo Audio signal can be extended up to 300 ft. when using 24Awg, Solid Wire UTP cable (Tripp Lite N022-01K-GY or N222-01K-GY); or, up to 400 ft. when using Zero-Skew UTP cable (Tripp Lite P524-01K)
- No external power required

## Specifications

General Info	
RoHS	Y
OVERVIEW	
Chromebook Compatible	No
Display Style	Splitter
Model Type	Component

### Highlights

- Remote extender wallplate for the B136-004 4-Port Extender/Splitter
- Extends a 1080i (60Hz) Component Video and Stereo Audio signal up to 300 ft. when using 24Awg, Solid Wire UTP cable
- Tripp Lite N022-01K-GY or N222-01K-GY; or, up to 400 ft. when using Zero-Skew UTP cable (Tripp Lite P524-01K)
- RJ45 Jack rear connection
- No external power required

### Package Includes

- B136-100-WP Component Video + Stereo Audio Remote Extender Wallplate
- Wallplate Mounting Screws
- Owner's Manual



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
[www.tripplite.com](http://www.tripplite.com)

Cable Types	CAT5/CAT5E
<b>CONNECTIONS</b>	
Side A - Connector 1	(x5) RCA Female
Side A - Connector 2	RJ45 Jack
<b>WARRANTY</b>	
Product Warranty Period (Worldwide)	1-year limited warranty

© 2015 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.