

## 2-Port DisplayPort to HDMI Splitter, Multi-display adapter, 3840x1200 at 60Hz

MODEL NUMBER: **B156-002-HDMI**



### Description

Tripp Lite B156-002-HDMI allows you to split or expand a DisplayPort audio/video signal on two HDMI monitors using standard HDMI cables (Tripp Lite P568-Series). You can choose to display the same image on both displays or expand it over both. Supports video resolutions up to 1920 x 1080 @ 60Hz (or 3840 x 1080 @ 60Hz when monitors are set to extended mode). The splitter can be located up to 16 ft. from the source and 35 ft. from the connected monitors. Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases.

### Features

- Splits a DisplayPort audio/video signal to two HDMI monitors, or expands the video over both
- Supports video resolutions up to 1920 x 1080 @ 60Hz (or 3840 x 1080 @ 60Hz when monitors are set to extended mode)
- Supports 30-bit Deep Color (10-bits per channel)
- Supports HDCP, EDID and DDC
- Supports DTS-HD, Dolby True HD and 7.1 channel surround sound audio
- A built-in booster allows the signal (up to 1920 x 1080 @ 60Hz) to be transmitted up to 35 ft. from the splitter
- Mounting hardware included for wall-mounting, rackmounting or pole-mounting
- Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases

### Highlights

- Splits a DisplayPort audio/video signal to two HDMI monitors, or expands the video over both
- Locate the monitor(s) up to 35 ft. from the splitter
- Supports 30-bit Deep Color (10-bits per channel)
- Supports HDCP, EDID and DDC
- Supports DTS-HD, Dolby True HD and 7.1 channel surround sound audio
- Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases

### System Requirements

- A DisplayPort equipped computer
- A DisplayPort equipped monitor
- For audio support, you must have a DisplayPort source that supports audio, and which has it enabled. Reference the FAQ in the Q&A tab of this page for details.

### Package Includes

- B156-002-HDMI Multi-Display Splitter/Expander
- Mounting Hardware
- External Power Supply (Input: 100-240V, 50/60Hz, 0.5A; Output: 5V, 2A)

## Specifications

OVERVIEW	
Display Style	Splitter
Model Type	HDMI



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
www.tripplite.com

Cable Type	CAT6
<b>PHYSICAL</b>	
Unit Dimensions (hwd / in.)	1.00 x 3.60 x 2.52
Unit Weight (lbs.)	1.0
Color	Black
<b>CONNECTIONS</b>	
Connector A	DISPLAYPORT (FEMALE)
Connector B	HDMI (FEMALE) (X2)
Ports	3
<b>WARRANTY</b>	
Product Warranty Period (Worldwide)	1-year limited warranty

© 2014 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.