

Performance you can trust

FLAWFINDER Cleaner Spray NDT Crack Detection System

Product Overview

FLAWFINDER CLEANER SPRAY is an aerosol applied cleaner used as part of the NDT crack detection system for pre-use cleaning, also for the easy removal of FLAWFINDER DYE PENETRANT and FLAWFINDER DEVELOPER Sprays.

The FLAWFINDER non-destructive inspection system is designed to provide a fast reliable method for visual detection of cracks or flaws which would not normally be visible to the naked eye. Ideal for the inspection of welded joints, castings, forgings on many different materials.

A bright red indication will mark the flaw or crack.

Features and Benefits

- Rapid and effective cleaning agent.
- Non-chlorinated solvent.
- Multi-angle valve system.
- Leaves no residue.

Directions for Storage and Use

- Shake aerosol well before use
- Apply from a distance of 15-30cm
- As with all products of this type it is recommended that compatibility with painted or coated surfaces, plastics and rubber be tested prior to use
- The storage temperature should be kept below +50°C, and the storage area should be out of direct sunlight
- Shelf life is 5 years from date of manufacture

Specification

Meets the requirements of **ISO 3452-2**

Pack Sizes

Pack Size	Part Code
300ml	63125

T +44 (0) 113 232 2600
F +44 (0) 113 232 2740
E customer-service@rocol.com
www.rocol.com

ROCOL House, Swillington, Leeds LS26 8BS

Registered Company No. 559693 VAT No. 742 0531 67
Registered Office: Admiral House, St Leonard's Road, Windsor, Berkshire SL4 3BL

ROCOL A division of **ITW** Ltd



FLAWFINDER Cleaner Spray NDT Crack Detection System

Application Method

Cleaning—Clean the area to be tested with FLAWFINDER CLEANER SPRAY and wipe thoroughly with a tissue or lint free cloth. Ensure the surface is clean, dry and free of contaminants. Repeat if necessary. After a final wipe, allow time to dry before using FLAWFINDER Dye Penetrant.

Apply Penetrant—Spray the test area and allow a minimum of 10 minutes contact time. Extremely fine definitions may take up to 30minutes.

Remove penetrant—Once the contact time has elapsed, the excess penetrant should be removed with a dry cloth, repeat if necessary. The remainder should be removed with a cloth pre-moistened with cleaner. Care is to be taken at this stage not to flush out the penetrant with cleaner as this will impair sensitivity. Repeat this procedure until surface penetrant is removed.

Develop—Shake the can well. Apply a thin film of FLAWFINDER Developer to the test area. Too much developer will mask indications. Leave for 10minutes to draw up the retained penetrant from any flaws or cracks. Larger cracks will show immediately, minute flaws or cracks may take a few minutes to develop the best indications.

Inspection—Suspect areas should be examined under natural or electric light for signs of flaws and cracks. Cracks will show up as lines whilst porosity will appear as pin holes.

If the results are inconclusive repeat the process taking greater care when removing the excess penetrant.

Property	Result
Propellant	CO ₂
Solvent	Blend of non-chlorinated hydrocarbons
Odour	Characteristic

Values quoted above are typical and do not constitute a specification.

Safety Data Sheets

Safety data sheets are available for download from our website www.ocol.com or may be obtained from your usual ROCOL contact.

The information in this publication is based on our experience and reports from customers. There are many factors outside our control or knowledge which affect the use and performance of our products, for which reason it is given without responsibility.

Issue:2 Date: 06-14

T +44 (0) 113 232 2600
F +44 (0) 113 232 2740
E customer-service@ocol.com
www.ocol.com

ROCOL House, Swillington, Leeds LS26 8BS

Registered Company No. 559693 VAT No. 742 0531 67
Registered Office: Admiral House, St Leonard's Road, Windsor, Berkshire SL4 3BL

ROCOL A division of **ITW** Ltd

