



- Protection level: IP20
 - Temperature range: -40°C ... +70°C

	All Dimensions in mm Original Size DIN A3		Scale 2:1	Free size tol.		Ref.	
	All rights reserved Department EC PD - RO		Created by MUNTEANV	Inspected by AVRAM	Standardisation HOFFMANN	Date 2014-11-19	State Final Release
HARTING Electronics GmbH D-32339 Espelkamp		Title RJ Industrial Cable Assembly				Doc-Key / ECM-Nr. 100155463/UGD/013/B 50000082085	
		Type TB	Number 09470400XXX			Rev. B	Page 1/2

1	2	3	4	5	6	7	8
A				90	09470400088		100
				89	09470400087		90
				88	09470400086		80
				87	09470400085		70
				86	09470400084		60
				85	09470400083		50
				84	09470400082		40
				83	09470400081		30
				82	09470400080		20
				81	09470400079		15
				80	09470400078		10
B	45	09470400044	100	79	09470400077		9
	44	09470400043	90	78	09470400076		8
	43	09470400042	80	77	09470400075		7
	42	09470400041	70	76	09470400074		6
	41	09470400040	60	75	09470400073		5
	40	09470400039	50	74	09470400072		4
	39	09470400038	40	73	09470400071		3
	38	09470400037	30	72	09470400070		2
	37	09470400036	20	71	09470400069		1.5
	36	09470400035	15	70	09470400068		1
	35	09470400134	12	69	09470400067		0.5
C	34	09470400034	10	68	09470400066		100
	33	09470400033	9	67	09470400065		90
	32	09470400032	8	66	09470400064		80
	31	09470400031	7	65	09470400063		70
	30	09470400030	6	64	09470400062		60
	29	09470400029	5	63	09470400061		50
	28	09470400028	4	62	09470400060		40
	27	09470400027	3	61	09470400059		30
	26	09470400026	2	60	09470400058		20
	25	09470400025	1.5	59	09470400057		15
D	24	09470400024	1	58	09470400056		10
	23	09470400023	0.5	57	09470400055		9
	22	09470400022	100	56	09470400054		8
	21	09470400021	90	55	09470400053		7
	20	09470400020	80	54	09470400052		6
	19	09470400019	70	53	09470400051		5
	18	09470400018	60	52	09470400050		4
	17	09470400017	50	51	09470400049		3
	16	09470400016	40	50	09470400048		2
	15	09470400015	30	49	09470400047		1.5
	14	09470400014	20	48	09470400046		1
	13	09470400013	15	47	09470400045		0.5
	12	09470400012	10	46	09470400145		0.3
E	11	09470400011	9	Cont. no.	Part no.	Type of cable	Dim. a[m]
	10	09470400010	8				
	9	09470400009	7				
	8	09470400008	6				
	7	09470400007	5				
	6	09470400006	4				
	5	09470400005	3				
	4	09470400004	2				
	3	09470400003	1.5				
	2	09470400002	1				
	1	09470400001	0.5				
F							

RJI Ethernet stranded cable,
4xAWG22/7, PVC, Cat. 5+, green

RJI Ethernet standard cable,
AWG22/1, 2x2x0.64, PVC, Cat. 5+, green

RJI Ethernet stranded cable,
AWG 22/7, 2x2x0.75, outdoor,
PVC, Cat. 5+, black

RJI Ethernet trailing cable,
AWG22/7, 2x2x0.75, PUR, Cat. 5+, green

	All Dimensions in mm Original Size DIN A3	Scale 1:1	Free size tol.	Ref.	
				Sub.	
	All rights reserved Department EC PD - RO	Created by MUNTEANV	Inspected by AVRAM	Standardisation HOFFMANN	Date 2014-11-19
		Title RJ Industrial Cable Assembly			State Final Release
HARTING Electronics GmbH D-32339 Espelkamp			Type TB	Number 09470400XXX	Doc-Key / ECM-Nr. 100155463/UGD/013/B 50000082085
				Rev. B	Page 2/2