

MODEL:

# SR42UWEXPNDNR3

## SmartRack™ White Heavy-Duty Open Frame Rack



42 Rack Units



3000 lb Stationary Load Capacity



3000 lb Rolling Load Capacity



Rolling Casters




Standard 19-inch Rack Width



Toolless Mounting Slots



Adjustable Rails with Easy-View Depth Index



Integrated Baying Tabs




Square Hole Mounting

- A** Adjustable Mounting Rails (4)
- B** Adjustable PDU Mounting Rails with Toolless Mounting Slots (2) (Hold up to 4 vertical PDUs)
- C** 3-Inch Heavy-Duty Casters (4)
- D** Heavy-Duty Levelers (4)

Also Includes: Owner's manual, 2 shipping/stabilizing brackets and rackmount equipment mounting hardware (50 cage nuts, 50 mounting screws, 50 nylon cup washers).

- Rack ships fully assembled for rapid deployment, but can be knocked down for easy reassembly in confined spaces
- Modular design optimized for quick configuration and reconfiguration
- Ideal for rackmount server, network and telecom applications



SEE NEXT PAGE FOR DETAILED UNIT MEASUREMENTS



1111 W. 35th Street  
Chicago, IL 60609 USA  
773.869.1234  
www.tripplite.com



### Specifications

Model	SR42UWEXPNDNR3
Rack Spaces	42U
Stationary Load Capacity	3000 lb (1363 kg)
Rolling Load Capacity	3000 lb (1363 kg)
Unit Dimensions (H x W x D)	79.5 x 23.63 x 43 in (2019 x 600 x 1092 mm)
Shipping Dimensions (H x W x D)	85 x 26 x 45.5 in (2159 x 660 x 1156 mm)
Unit Weight	150 lb (68 kg)
Shipping Weight	200 lb (90.7 kg)
Certifications	Tested to: EIA-310-E, IEC 60297-3-100, DIN 41494, UL 60950, RoHS, NOM

Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice.



Also Available: Shock pallet models with special packaging to facilitate equipment pre-installation and reshipment to final site. Heavy-duty shock pallet holds up to 1250 lb (568 kg), including the weight of the rack and pre-installed equipment. Add "SP1" to model numbers above to order shock pallet models.



Dimensions: [mm] INCHES

Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice.

MODEL:  
**SR42UWEXPNDNR3**

**TRIPP-LITE**

1111 W. 35th Street  
Chicago, IL 60609 USA  
773.869.1234

[www.tripplite.com](http://www.tripplite.com)