

AXIS T92A Housing Series

Protective housings for Axis network cameras.



- > Indoor and outdoor installation
- > Easy installation
- > Aluminum casing
- > IP66-rated protection

AXIS T92A Housing Series protects the Axis network camera in outdoor and adverse indoor conditions.

AXIS T92A Housing Series is tailor-made for Axis fixed network cameras. These housings have a side opening and are made of die-cast aluminum, offering an IP66-rated protection against dust and heavy rain.

AXIS T92A Housing Series is available in three models: AXIS T92A00 with a pre-installed power supply, AXIS T92A10 with pre-installed 24 V AC power connection board and AXIS T92A20 with pre-installed High Power over Ethernet splitter, for quick and easy installation. The splitter provides power both for the camera and for heating the housing, eliminating the need for additional power cables.

The included sunshield, with its integrated edge-protector, offers good thermal insulation, enabling the Axis network camera to operate in temperatures ranging from -20 °C up to 50 °C (-4 °F to 122 °F).

Various brackets and accessories are available for AXIS T92A Housing Series.

Supported cameras are AXIS Q1755 and indoor models of AXIS P13 and AXIS Q16 Network Cameras.




Technical Specifications – AXIS T92A Housing Series

| | | | |
|--------------------------|---|-----------------------------|--|
| Models | AXIS T92A00 Housing (not for US market) AXIS T92A10 Housing (only for US market) AXIS T92A20 Housing (available in all Regions) | Environment | Indoor/outdoor |
| General | | Operating conditions | -20 °C to 50 °C (-4 °F to 122 °F) |
| Supported cameras | AXIS Q1755, AXIS Q16 (Indoor models), AXIS P13 (indoor models) | Approvals | EN 61000-6-3, EN 60950, EN 50130-4 |
| Casing | Die-cast aluminum, Sunshield in ABS IP66-rated Color: White RAL9002 3 removable cable glands (2xPG9 & 1xPG11) | Weight | 3 kg (6.6 lb) included sunshield |
| Power | AXIS T92A00: 230 V AC / 44 W AXIS T92A10: 24 V AC / 44 W AXIS T92A20: Axis 30 W midspans | Included accessories | Sunshield, Heater and thermostat, Installation kit for camera, Installation Guide, Wall bracket AXIS T92A10: 110 V AC to 24 V AC transformer AXIS T92A20: Axis 30 W midspan |

More information is available at www.axis.com

Dimensions

mm (inch)



Optional accessories

Wall brackets,

Ball joint

1. With integrated junction box

2. Ball joint

3. With internal cable channel

Ceiling brackets,

Ball joint

4. With internal cable channel

5. Ball joint

6. Ball joint

7. Column mount



Wall bracket accessories

1. Adapter plate

2. Pole adapter

3. Corner mount



Other accessories

1. Waterproof junction box

