


GigaMax® CAT 5e SlimLine Boot UTP Patch Cords

APPLICATION

Leviton SlimLine Boot Patch Cords feature a narrow profile to support high-density panels and switches. The snagless plug design makes the patch cords an excellent choice in environments where moves, adds, and changes are frequent.



SPECIFICATION

Patch cords shall meet or exceed requirements for CAT 5e performance described in ANSI/TIA-568-C.2. Patch cords shall be stranded conductor with an 8-position modular plug on each end. The cords shall be available in lengths of 3, 5, 7, and 10 feet. Patch cords shall include a narrow-profile boot and a snag-free latch. Patch cord plug shall have industry-standard, ANSI/TIA-1096-A compliant 50 micro inches of gold plating.

FEATURES

- Independently tested and verified by Intertek (ETL) for CAT 5e component performance
- Improved plug access in tight spaces
- Snagless plug design
- Stranded conductor for longer flex-life
- Improved strain relief

DESIGN CONSIDERATIONS

- ANSI/TIA channel performance limits total length of patching and equipment cords to 32 feet (10 meters) per ANSI/TIA-568-C.2
- A variety of colors for color coding or organization
- Available in four standard lengths (custom lengths also available)

STANDARDS COMPLIANCE

- ANSI/TIA-568-C.2
- ISO/IEC 11801
- ANSI/TIA-1096-A (formerly FCC Part 68)
- cULus Listed
- RoHS
- UL 444 CM rated

PHYSICAL SPECIFICATIONS

Dimensions:	See page two
Outer Diameter (O.D.):	0.22"
Materials:	24-gauge, UTP stranded conductor, modular non-keyed, 8-position, 8-conductor plug, 94V-0 rated
Colors:	White, Yellow, Blue, Green, Grey

COUNTRY OF ORIGIN

China


WARRANTY INFORMATION

For a copy of Leviton product warranties, visit www.leviton.com/warranty.

5D460-xx*

ELECTRONIC FILES

For CAD files, typical specs, or technical drawings (.DXF, .DWG), visit www.leviton.com.



O.D.: 0.22"

5D460-XX*

PART NUMBERS

Description	Part No.
GigaMax® CAT 5e SlimLine Boot UTP Patch Cord, 3-foot length (0.9m)	5D460-03*
GigaMax CAT 5e SlimLine Boot UTP Patch Cord, 5-foot length (1.5m)	5D460-05*
GigaMax CAT 5e SlimLine Boot UTP Patch Cord, 7-foot length (2.1m)	5D460-07*
GigaMax CAT 5e SlimLine Boot UTP Patch Cord, 10-foot length (3.0m)	5D460-10*

* = Colors: White (W), Yellow (Y), Blue (L), Green (G), Grey (S)



For assistance customizing your patch cords, please visit
www.leviton.com/configurator or call Tech Support at 800.824.3005.