

eXtreme® CAT 6+ Shielded Patch Cords

APPLICATION

eXtreme CAT 6+ Shielded Patch Cords exceed all performance requirements for internal parameters up to 250 MHz. Shielded patch cords protect critical data from EMI (electromagnetic interference) and RFI (radio frequency interference). The patch cords are part of the Leviton shielded solution for use in healthcare, transportation, government, military, manufacturing, casinos, and other environments where EMI/RFI may be a concern. Shielded solutions are Rockwell Automation Encompass™ approved.



SPECIFICATION

The CAT 6 shielded patch cord shall meet or exceed applicable electrical performance standards for all internal parameters up to 250 MHz. The patch cord shall be a 26-gauge FTP construction with stranded conductors to provide greater flex-life. The patch cords shall be available in standard lengths of 3, 5, 7, 10, 15, and 20 feet.

FEATURES

- Strain-relief boot ensures long-term network performance
- Stranded 26-gauge conductors provides longer flex-life
- FTP construction provides excellent EMI/RFI protection
- Snagless boot design prevents tab breakage during moves, adds, and changes
- Six standard lengths

STANDARDS COMPLIANCE

Leviton CAT 6 Shielded Patch Cords are part of a complete shielded solution that meets the following:

- ANSI/TIA-568-C.2
- ANSI/TIA-1096-A
- Intertek (ETL) third-party verification
- ISO 11801 Class E
- UL 444 CM rated

PERFORMANCE SPECIFICATIONS

Available Lengths:	See page two
Outer Diameter (O.D.):	0.240"
Materials:	26-gauge, stranded conductor
Color:	Grey

COUNTRY OF ORIGIN


Taiwan

WARRANTY INFORMATION

For a copy of Leviton product warranties, visit www.leviton.com/warranty.

ELECTRONIC FILES

For CAD files, typical specs, or technical drawings (.DXF, .DWG), visit www.leviton.com.



6S460-xxS

PART NUMBERS

Description	Part No.
eXtreme® CAT 6+ Shielded Patch Cord, grey, 3-foot length (0.9m)	6S460-03S
eXtreme CAT 6+ Shielded Patch Cord, grey, 5-foot length (1.5m)	6S460-05S
eXtreme CAT 6+ Shielded Patch Cord, grey, 7-foot length (2.1m)	6S460-07S
eXtreme CAT 6+ Shielded Patch Cord, grey, 10-foot length (3.0m)	6S460-10S
eXtreme CAT 6+ Shielded Patch Cord, grey, 15-foot length (4.6m)	6S460-15S
eXtreme CAT 6+ Shielded Patch Cord, grey, 20-foot length (6.1m)	6S460-20S