



## N Male Connector for 1/2" Coaxial Cable, OMNI FIT™ Premium, Straight, Polymer claw and compression sealing

OMNI FIT™ high performance connectors are designed for use with both CELLFLEX® (copper) and CELLFLEX® Lite (aluminium) cables. They are designed specifically to provide the highest quality connector-cable interface while simplifying and speeding up connector attachment. All RFS connectors are fully tested for mechanical and electrical compliance to industry specifications. The 7-16 connector is the most rugged RF connection meeting all requirements even under the most severe environmental conditions. Sealing against outer conductor and jacket by means of the polymer claw and 360° compression fit. Multifunctional, self-lubricating HighTech polymer assembly locks on cable corrugation, avoids electrochemical potential differences and compression-fits to the jacket.



OMNI FIT™ Premium Connectors

### FEATURES / BENEFITS

Ultra high PIM performance i.e. reduced interference leading to high customer satisfaction

## Technical Features

### GENERAL SPECIFICATIONS

Transmission Line Type		Coaxial Cable
Cable Size		1/2"
Cable Type		Foam Dielectric
Model Series		LCF12-50 Series
Connector Interface		N
Connector Type		OMNI FIT™ PREMIUM Straight
Sealing Method		Polymer claw + 360° Compression
Gender		Male

### ELECTRICAL SPECIFICATIONS

Nominal Impedance	Ohm	50
3rd Order IM Product @ 2x20 Watts	dBc	-156 ; typical -162
Maximum Frequency	GHz	3.7
VSWR, Return Loss	VSWR (dB)	0 < f ≤ 1.0 GHz: 1.020 (40.0) 1.0 < f ≤ 2.7 GHz: 1.030 (36.6) 2.7 < f ≤ 3.7 GHz: 1.060 (30.7)

### MECHANICAL SPECIFICATIONS

Plating Outer/Inner		NiTin/Silver
Length	mm (in)	64.05 (2.52)
Outer Diameter	mm (in)	29 (1.14)
Weight	kg (lb)	0.11 (0.24)
Inner Contact Attachment		Basket
Outer Contact Attachment		360° clamping

### ACCESSORIES


Wrench size front	mm (in)	18
Wrench size rear	mm (in)	26
Trimming Tool		TRIM-SET-L12-D01 TRIM-LCF12-D01-A

### TESTING AND ENVIRONMENTAL


Waterproof Level		IP68
------------------	--	------



**N Male Connector for 1/2" Coaxial Cable, OMNI FIT™ Premium,  
Straight, Polymer claw and compression sealing**



Cut NM-LCF12-D01\_DRW.PNG



View NM-LCF12-D01\_DRW.PNG

**External Document Links**

Installation Instruction

**Notes**