


## QuickPort® Fiber Optic Adapters ST, SC, LC, and MTP®

### APPLICATION

QuickPort Fiber Optic Adapters provide connectivity for workstation cabling termination on single-mode and multimode fiber cable. QuickPort bulkhead modules snap into any housing with the QuickPort name: flush- and surface-mount outlets, Multimedia Outlet System (with adapter), patch panels, and patch blocks.



### SPECIFICATION

QuickPort Fiber Optic Adapters for fiber optic cabling media shall be individual snap-in style and shall fit into QuickPort panels. The LC, SC, and ST Adapters shall be compatible with single-mode, multimode, and laser-optimized multimode connectors, and available in zirconia ceramic or phosphor bronze sleeves. ST and SC QuickPort Adapters shall be available in standard colors of ivory, white, grey, and black. SC QuickPort Adapters shall also be available in blue for UPC and green for SC/APC identification in single-mode applications. LC QuickPort housings shall be available in standard colors as well as blue, yellow, red, green, and orange as part of the Secure Keyed LC system. MTP QuickPort housings shall be available in black and white.

### DESIGN CONSIDERATIONS

- Quickport adapters snap into QuickPort panels or modules
- ST and SC QuickPort Adapters are available in standard colors of ivory, white, grey, and black
- SC QuickPort Adapters are also available in blue or green for identification in single-mode applications
- LC QuickPort adapters are available in standard colors as well as blue, yellow, red, green, and orange as part of the Secure Keyed LC System
- Use in permanent or temporary applications
- ST, SC, and LC QuickPort Adapters are available in zirconia ceramic or phosphor bronze sleeves, and are compatible with single-mode, multimode, and laser optimized (LC only)

### STANDARDS COMPLIANCE

ANSI/TIA-568-C.3, TIA 604

### PHYSICAL SPECIFICATIONS

Dimensions:

ST Adapter:	.63" H x .58" W x 1.15" D
SC Adapter:	.63" H x .58" W x 1.35" D
SC/APC Adapter:	.63" H x .58" W x 1.04" D
LC Adapter:	.63" H x .58" W x 1.15" D
MTP Adapter:	.63" H x .58" W x .79" D

Materials:

QuickPort Housing	Snap-in module bodies are high-impact, fire-retardant plastic rated UL 94V-0
ST Fiber Adapter	Single-mode: zirconia sleeve Multimode: phosphor bronze sleeve
SC Fiber Adapter	Single-mode: zirconia sleeve Multimode: phosphor bronze sleeve
LC Fiber Adapter	Single-mode: zirconia sleeve LOMM: zirconia sleeve Multimode: phosphor bronze sleeve






### WARRANTY INFORMATION

For a copy of Leviton product warranties, visit [www.leviton.com](http://www.leviton.com).

### ELECTRONIC FILES

For CAD files, typical specs, or dimensional line art (.DXF, .DWG, Visio), visit [www.leviton.com](http://www.leviton.com).

<b>Leviton Network Solutions</b> 2222 - 222nd St. SE Bothell, WA 98021-4416  tel 1-800-824-3005 tel +1-425-486-2222 appeng@leviton.com www.leviton.com	<b>Asia / Pacific</b> T +1.631.812.6228 E infoasean@leviton.com	<b>Canada</b> T +1.514.954.1840 E pcservice@leviton.com	<b>Caribbean</b> T +1.954.593.1896 E infocaribbean@leviton.com	<b>China</b> T +852.2774.9876 E infochina@leviton.com	<b>Colombia</b> T +57.1.743.6045 E infocolombia@leviton.com
	<b>Europe</b> T +33.6.8869.1380 E infoeurope@leviton.com	<b>India / SAARC</b> T +971.4.886.4722 E infoindia@leviton.com	<b>Mexico</b> T +52.55.5082.1040 E lsamarketing@leviton.com	<b>Middle East &amp; Africa</b> T +971.4.886.4722 E lmeinfo@leviton.com	<b>South Korea</b> T +82.2.3273.9963 E infokorea@leviton.com



**QUICKPORT FIBER ADAPTERS\***

DESCRIPTION	PART NO.
QuickPort Duplex LC Adapter, MM, phosphor bronze sleeve, beige	41085-ML*
QuickPort Duplex LC Adapter, 10G LOMM, zirconia ceramic sleeve, aqua	41085-LL*
QuickPort Duplex LC Adapter, SM, zirconia ceramic sleeve, blue	41085-SL*
QuickPort Simplex SC Adapter, MM, phosphor bronze sleeve, female front/back	41085-M`C
QuickPort Simplex SC Adapter, SM, zirconia ceramic, female front/back	41085-S`C
QuickPort Simplex SC Adapter, SM, zirconia ceramic, female front/back, blue	41085-SLC
QuickPort Simplex SC Adapter, SM/APC, zirconia ceramic, female front/back	41085-AS`
QuickPort ST Fiber Optic Adapter, MM, phosphor bronze sleeve	41084-S`F
QuickPort ST Fiber Optic Adapter, SM, zirconia ceramic sleeve	41084-S`Z
MTP® QuickPort Adapter, SM/MM	41085-TP†

\* = Colors: Ivory (I), White (W), Grey (G), Black (E), Yellow (Y), Red (R), Blue (B), Green (V), Orange (O)  
` = Colors: Ivory (I), White (W), Grey (G), Black (E)  
† = Colors: White (W), Black (E)

^ Minimum order quantity and lead times may apply.



**Leviton Network Solutions**  
2222 - 222nd St. SE  
Bothell, WA 98021-4416

**Asia / Pacific**  
T +1.631.812.6228  
E infoasean@leviton.com

**Canada**  
T +1.514.954.1840  
E pcservice@leviton.com

**Caribbean**  
T +1.954.593.1896  
E infocaribbean@leviton.com

**China**  
T +852.2774.9876  
E infochina@leviton.com

**Colombia**  
T +57.1.743.6045  
E infocolombia@leviton.com

tel 1-800-824-3005  
tel +1-425-486-2222  
appeng@leviton.com  
www.leviton.com

**Europe**  
T +33.6.8869.1380  
E infoeurope@leviton.com

**India / SAARC**  
T +971.4.886.4722  
E infoindia@leviton.com

**Mexico**  
T +52.55.5082.1040  
E lsamarketing@leviton.com

**Middle East & Africa**  
T +971.4.886.4722  
E lmeinfo@leviton.com

**South Korea**  
T +82.2.3273.9963  
E infokorea@leviton.com