

Technical Data

ROCOL®

Performance you can trust



INDUSTRIAL CLEANER RAPID DRY Spray



Fast evaporating multi-purpose cleaner

Product Overview

ROCOL® INDUSTRIAL CLEANER Rapid Dry Spray is a solvent based cleaner in aerosol format. It is NSF K1 registered as suitable for use on food processing equipment and utensils.

INDUSTRIAL CLEANER Rapid Dry Spray is also ideal for use in many other industrial environments.

INDUSTRIAL CLEANER Rapid Dry Spray contains a blend of solvents to clean a wide variety of workplace grime and residues, evaporating rapidly to leave no residue.

Features and Benefits

- INDUSTRIAL CLEANER Rapid Dry Spray has metal detectable plastic components (aerosol caps and actuators) capable of detection by most metal detection equipment.
- It is a foodsafe cleaner designed to cut through all general grime, grease, dirt and other workplace contamination.
- INDUSTRIAL CLEANER Rapid Dry Spray is a fast evaporating cleaner which dries rapidly and completely leaving a residue free surface.
- It has a 360° valve system enabling it to be sprayed from any angle.
- INDUSTRIAL CLEANER Rapid Dry Spray has a blue mini-jet spray nozzle for accurate application and easy identification as a foodsafe product.

Directions for Storage and Use

- Shake aerosol well before use.
- Test compatibility with plastics and rubbers and painted or coated surfaces prior to application.
- Apply from a distance of 15 – 30 cm.
- The aerosol can be sprayed at any angle due to 360° valve technology.
- The cleaning operation may be enhanced by working the solvent into the surface using a clean, dry cloth.
- For heavier contamination, reapplication may be required.
- Cleaned components should be rinsed before returning to a food processing area.
- Extremely flammable - Use only in well ventilated areas and do not apply to very hot surfaces.
- Store below +50°C, out of direct sunlight.
- Shelf life is 5 years from date of manufacture.
- Consult safety data sheet before use.

Specifications

- ROCOL INDUSTRIAL CLEANER Rapid Dry Spray does not contain: mineral hydrocarbons, animal derived materials, nut oils or genetically modified ingredients.
- NSF K1 Registered - 135883

Pack Sizes

Pack Size	Part Code
300ml	34131

T +44 (0) 113 232 2600
F +44 (0) 113 232 2740
E customer-service@rocol.com
www.rocol.com

ROCOL House, Swillington, Leeds LS26 8BS

Registered Company No. 559693 VAT No. 742 0531 67
Registered Office: Admiral House, St Leonard's Road, Windsor, Berkshire SL4 3BL

ROCOL A division of **ITW** Ltd



Performance you can trust



INDUSTRIAL CLEANER RAPID DRY Spray

Fast evaporating multi-purpose cleaner

Property	Test Method	Result
Appearance	Visual	Colourless liquid
Propellant	N/A	Carbon dioxide (CO ₂)
Solvent	N/A	Blend of hydrocarbon and alcohol
Flash Point (°C)	PMCC	<0°C
Odour	N/A	Characteristic
Water Solubility	N/A	Partially soluble
Density (kg/m ⁻³)	RTM 3	0.74
Metal Detection:		
Aerosol Cap	Equivalent sphere size	>3.0mm
Actuator	Equivalent sphere size	>3.0mm

Values quoted above are typical and do not constitute a specification.

INDUSTRIAL CLEANER RAPID DRY Spray is produced at a Halal Control Certified Site (Swillington UK) and is certified as Halal only where the Halal Control Logo is displayed on the product label (certificate registration number C-912-350-05-01/1).



Metal detectable caps to reduce potential contamination risk.

Safety Data Sheets

Safety data sheets are available for download from our website www.rocol.com or may be obtained from your usual ROCOL contact.

The information in this publication is based on our experience and reports from customers. There are many factors outside our control or knowledge which affect the use and performance of our products, for which reason it is given without responsibility.

Issue: 3 Date: 07-15

T +44 (0) 113 232 2600
F +44 (0) 113 232 2740
E customer-service@rocol.com
www.rocol.com

ROCOL House, Swillington, Leeds LS26 8BS

Registered Company No. 559693 VAT No. 742 0531 67

Registered Office: Admiral House, St Leonard's Road, Windsor, Berkshire SL4 3BL

ROCOL A division of **ITW** Ltd

