


# STI CLOCK/BELL DAMAGE STOPPER®



STI-9632



STI-9631-R

## PRODUCT OVERVIEW

These super tough wire guards are designed to protect clocks, bells and similar instruments. Three sizes are available to cover a wide range of units. Each is constructed of 9-gauge steel wire with corrosion resistant polyester coating. Their octagon, spiderweb like shape also helps them take tough knocks in stride.

## BACKED BY A THREE YEAR GUARANTEE

As all STI protective wire guards, these Stoppers are backed by a three year guarantee against breakage in normal use. Also, because they are white in color, users report that their clock numbers are easier to see than with darker competitive guards. Installation is easy and tamper resistant hardware (screws and bits) are available.

## KEY FEATURES

### General Information

- Guards help protect against vandalism and accidental damage.
- Three year guarantee against breakage in normal use.

### Construction

- Weblike octagon shape of 9-gauge coated steel wire makes them extremely difficult to break.

### Installation

- Fast and easy installation.
- Simple removal for servicing or routine maintenance.
- May be painted prior to installation to match decor.

### Options

- Tamper resistant hardware (screws and bits) are available.
- Three models to fit a wide range of units (both clocks and bells).



For more information, call 1-800-888-4784 (4STI) or visit [www.sti-usa.com](http://www.sti-usa.com)



**Safety Technology  
International, Inc.**

# STI Clock/Bell Damage Stopper®

## Dimensions and Technical Information


### MODELS AVAILABLE

|                     |  |
|---------------------|--|
| <b>STI-STI-9631</b> | Clock/Bell Damage Stopper  |
| <b>STI-9631-R</b>   | Clock/Bell Damage Stopper - red  |
| <b>STI-9631-SS</b>  | Clock/Bell Damage Stopper - stainless steel                                    |
| <b>STI-9632</b>     | Clock/Bell Damage Stopper  |
| <b>STI-9632-SS</b>  | Clock/Bell Damage Stopper - stainless steel                                    |
| <b>STI-9633</b>     | Clock/Bell Damage Stopper  |
| <b>SUB-82</b>       | Tamper resistant stainless steel screws, #8 x 1<br>1/2" snake eye (quantity 4) |
| <b>19038</b>        | 5/16 in. hex drive tamper bit for tamper<br>resistant screws                   |

### WARRANTY

Three year guarantee against breakage in normal use.

| MODEL    | DEPTH         | DIAMETER         |
|----------|---------------|------------------|
| STI-9631 | 6 in. (152mm) | 10.5 in. (267mm) |
| STI-9632 | 6 in. (152mm) | 16.5 in. (419mm) |
| STI-9633 | 6 in. (152mm) | 20 in. (508mm)   |



STI CLOCK/BELL GUARD



**Safety Technology  
International, Inc.**

2306 Airport Road  
Waterford, Michigan  
48327, USA

Tel: 248-673-9898  
Fax: 248-673-1246  
Toll-free: 800-888-4784  
info@sti-usa.com  
www.sti-usa.com

Unit 49G Pipers Road  
Park Farm Industrial Estate  
Redditch, Worcestershire  
B98 0HU England

Tel: 44 (0) 1527 520 999  
Fax: 44 (0) 1527 501 999  
info@sti-europe.com  
www.sti-europe.com