

STI MOUNTING PEDESTAL



STI-9779



STI-9780

PRODUCT OVERVIEW

This pedestal helps provide convenience for security and/or access control equipment. The heavy gauge steel pedestal can be used for: access control, telephone entry, gate operators, parking control, card readers, push buttons/switches, intercoms, fire access stations, keypads and much more.

Two models are available. The STI-9779 measures 60 inches (1524mm) high and is designed to be buried into the ground. The STI-9780 measures 42 inches (1067mm) high and is designed with a base to mount to a concrete pad. This unit has a mounting flange cover plate which helps protect the four (4) mounting nuts from damage. The posts for both models measure 2 x 2 inches around.

KEY FEATURES

General Information

- Can be used with a variety of access control equipment.
- Provides convenience and security.

Design

- Smooth radius bend.

Construction

- Heavy gauge steel construction.
- Durable anti-corrosive polyester powder coat finish.

Installation

- Mounting plate hole pattern supports a variety of appliances.

Options

- Two models - surface and subsurface mount.



For more information, call 1-800-888-4784 (4STI) or visit www.sti-usa.com



**Safety Technology
International, Inc.**

STI Mounting Pedestal

Dimensions and Technical Information

MODELS AVAILABLE

- STI-9779** Mounting Pedestal - Subsurface mount
STI-9780 Mounting Pedestal - Surface mount

Accessory:

- SUB-318** Adapter plate used for mounting "A", "B" or "F" back box to pedestal


STI covers that mount to pedestal:

Polycarbonate Enclosure

- STI-7500A** With Enclosed Deep Back Box, Interior Key Lock
STI-7500B With Enclosed Back Box and Double-Gang Electrical Box, Interior Key Lock
STI-7500F With Enclosed Back Box, Interior Key Lock
STI-7501A With Enclosed Deep Back Box, Interior Thumb Lock
STI-7501B With Enclosed Back Box and Double-Gang Electrical Box, Interior Thumb Lock
STI-7501F With Enclosed Back Box, Interior Thumb Lock
STI-7510A With Enclosed Deep Back Box, Exterior Key Lock
STI-7510B With Enclosed Back Box and Double-Gang Electrical Box, Exterior Key Lock
STI-7510F With Enclosed Back Box, Exterior Key Lock
STI-7511A With Enclosed Deep Back Box, Exterior Thumb Lock
STI-7511B With Enclosed Back Box and Double-Gang Electrical Box, Exterior Thumb Lock
STI-7501F With Enclosed Back Box, Exterior Thumb Lock

Access Control Housing

- STI-7515A** With "A" Back Box (allows 4.25" of depth)
STI-7515F With "F" Back Box (allows 2" of depth)



**Safety Technology
International, Inc.**

2306 Airport Road
Waterford, Michigan
48327, USA

Tel: 248-673-9898
Fax: 248-673-1246
Toll-free: 800-888-4784
info@sti-usa.com
www.sti-usa.com

Unit 49G Pipers Road
Park Farm Industrial Estate
Redditch, Worcestershire
B98 0HU England

Tel: 44 (0) 1527 520 999
Fax: 44 (0) 1527 501 999
info@sti-europe.com
www.sti-europe.com