

STI UNIVERSAL BUTTON



UB-1



UB-1/LTUL



KEY FEATURES

General Information

- Offers over 300 different combinations.
- Momentary button offers many options to provide just what a customer wants in one convenient package.
- 100,000 operations.
- One year guarantee on electro mechanical and electronic components.

Construction

- Faceplate constructed of cast aluminum.
- UL Listed to U.S. and Canadian safety standards.

Installation

- Temperature: -40° to 185° F (-40° to 85°C).
- Mounts to standard electrical handi box.
- Single gang plate slightly oversized to cover old plate installation marks.

Electronics

- Illuminated 12/24 volt LED button and illuminated message light kit.
- Two sets of independent Form "C" contacts.
- Contacts rated at 10A, 1/2 HP, 125/250 VAC, 6A, 30V.

Options

- Five inserts for the button included – EXIT, PUSH, PUSH TO EXIT, handicap symbol and blank.
- Three different lens covers included – red, green and blue.
- Ten color coated message inserts in green, blue, yellow and white.
- Plate messages inscribed with EXIT, EMERGENCY and translucent blanks (allowing for custom labels).

PRODUCT OVERVIEW

This momentary button helps eliminate having to stock dozens of push buttons, and wasting precious time and money tracking down just the right button for a customer. It offers many options to provide just what a customer wants in one convenient package. Button is ready to be assembled out of box and is easily installed within minutes on site.

Universal Button offers over 300 different combinations for the price of a standard one configuration button. The faceplate is constructed of cast aluminum metal, allowing it to take tough knocks in stride, and is slightly oversized to cover old plate installation marks. Button package includes: faceplate, three illuminated push buttons, five changeable button messages and ten changeable illuminated activation messages.

HOW IT WORKS

The installer simply has to choose which lens cover, button insert and interchangeable message plate works best for the customers need, and easily snap them in place. This allows the button to be mounted in a matter of minutes instead of waiting weeks for a specific button to be ordered and delivered.



For more information, call 1-800-888-4784 (4STI) or visit www.sti-usa.com



Safety Technology International, Inc.

STI Universal Button

Dimensions and Technical Information

MODELS AVAILABLE

UB-1	Universal Button
UB-2	2" Universal Button
UB-1/LTUL*	Universal Button with UL Latching Timer
UB-2/LTUL*	2" Universal Button with UL Latching Timer

Accessories

LT-1	Latching/Timer Module
UB-2LENS	2" Lens
UB-1CL-Color	Custom Label applied to blank, changeable message plates (blue, green, white or yellow)
SUB-UB-1C	Contact Block
SUB-71102A-Color	Color Match Back Box Kit (red, blue, green, white or yellow)
10147	24 Volt LED, White (standard)
10145	24 Volt LED, Red
10141	24 Volt LED, Blue
10143	24 Volt LED, Green
10144	12 Volt LED, Red
10140	12 Volt LED, Blue
10142	12 Volt LED, Green
STI-6518	Bopper Stopper® Protective Cover
STI-6600-Color	Mini Stopper® II with Horn (blue, green, white or yellow)

*See LT-1 for complete latching/timer information

APPROVALS & WARRANTY



TESTING

It has been tested and approved or listed by:

- UL/cUL File S7255, Volume 2
- ADA for operation

WARRANTY

One year guarantee on electro mechanical and electronic components.



**Safety Technology
International, Inc.**

2306 Airport Road
Waterford, Michigan
48327, USA

Tel: 248-673-9898
Fax: 248-673-1246
Toll-free: 800-888-4784
info@sti-usa.com
www.sti-usa.com

Unit 49G Pipers Road
Park Farm Industrial Estate
Redditch, Worcestershire
B98 0HU England

Tel: 44 (0) 1527 520 999
Fax: 44 (0) 1527 501 999
info@sti-europe.com
www.sti-europe.com