



## Professional Solutions - Unrivalled Value

Adjustable height ceiling mount for 10" to 32" flat panel screens, allows a different mounting solution when wall mounting is not an option. Continuous tilt of 25° forward, 360° rotation and post-installation leveling with telescoping adjustable drop lengths to provide perfect screen positioning. Makes a secure installation quick and easy, simply hang the screen and attach bottom screws to lock in place.

10"-32" / 25.4cm-81.3cm

40 LB / 18 KG

### Functional Specifications

Tilt: +25°-0°

Rotation: 360°

**Mounting Surfaces:** Structural wood beams (with included hardware), concrete & other structural surfaces (additional hardware or accessories required).

**MaxMountingPattern:**

100mm (3.9") width

100mm (3.9") height

**Drop Length:** 2' - 4'

**Load Capacity:** 40 LB / 18 KG

**Warranty:** Limited 10 Years

### Screen Size Variety

Fits most 10" to 32" flat panel screens weighing 40lb or less.

### VESA Compatible

Fits VESA hole patterns with 75x75mm and 100x100mm sizes.

### Height Adjustment

Telescoping adjustment from 2' to 4'.

### Cable Management

Easily route cables through openings at the top and bottom of the extension column.

### Multi-Angle Positioning

Up to 25° of continuous tilt and 360° rotation.

### Decorative Cover

Conceals ceiling adapter for a clean look.

### Included Hardware


Pre-sorted hardware pack for easy component selection and installation (hardware for installation to wood studs or concrete surfaces included).

**Decorative Cover**  
Conceals ceiling adapter for a clean look.



**VESA Compatible**  
Fits VESA hole patterns with 75x75mm and 100x100mm sizes.

**Adjustable Drop Length**  
Telescoping adjustment without use of tools.



**Tilt**  
0° to +25° tilt for optimal viewing angles.







**Mounting Hardware**  
Complete set of screen mounting hardware, labeled for ease of use and ready to go.



# Flat Panel Ceiling Mount

For 10" to 32" (25.4-81.3cm) LCD and Plasma TVs

CV100S-24A (BLACK)  
CV100S-24AW (WHITE)




## Product Specifications

PRODUCT WEIGHT	LOAD CAPACITY	COLORS	FINISH
3.1lb (1.4kg)	40lb (18kg)	Black White	Scratchresistant powdercoating

## Package Specifications

PACKAGE SIZE (WxHxD)	SHIP WEIGHT	UPC CODE	PACKAGE CONTENTS
11" x 8" x 3"	4.6lb (2.1kg)	CV100S-24A(Black) 0815885014857	Ceiling adapter, adjustable column, mount box, mounting hardware, manual.
		CV100S-24AW(White) 0815885014888	

## Mounting Interface



Max Mounting Pattern  
100mm (W) x 100mm (H)

VESA W 75mm 100mm  
X 75mm 100mm  
H 75mm 100mm

Visit [crimsonav.com](http://crimsonav.com) to see the complete lineup of TV, Monitor, Display, and Projector mounts. © 2013 Crimson AV LLC. All rights reserved.

[www.crimsonav.com](http://www.crimsonav.com) | ph: 866.668.6888 | fax: 847.919.3483 | [support@crimsonav.com](mailto:support@crimsonav.com)