


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



PANDUIT P/N	WEIGHT
T70PG	.049 LB (22.1 g)
OF70PG	

C


E

NOTES:

1. SEE CURRENT CATALOG FOR ADDITIONAL PART SUFFIXES TO INDICATE COLOR AND/OR PACKAGE QUANTITY.
2. THE T70PG FACEPLATE CAN BE USED WITH PANDUIT SURFACE RACEWAY SYSTEMS AND BOXES THAT ACCEPT 70mm SNAP-ON FACEPLATES (INCLUDES: T-70, TWIN-70, TE70, TG-70, ETC)
3. THIS PRODUCT ACCOMMODATES GFCI AND RECTANGULAR RECEPTACLES.
4. DIMENSIONS IN PARENTHESES ARE IN METRIC.
5. THE OF70PG FACEPLATE CAN BE USED WITH PANDUIT OFFICE FURNITURE CORNER RACEWAY (OFCR70) AND DESK MOUNT BOX (OFR20DMB).

B

D



CAD FILENAME/LAYERS

D36572BN_DC_T70PG_02A.prt

PANDUIT

CORP. TINLEY PARK, ILLINOIS

T-70 SNAP-ON CLASSIC SERIES
GFCI FACEPLATE (T70PG & OF70PG)
CUSTOMER DRAWING

UNLESS OTHERWISE SPECIFIED,
DIMENSIONAL TOLERANCES ARE:
(.X) ± (.XXX) ±
(.XX) ±.03(.8) ANGLES ±

UNLESS OTHERWISE SPECIFIED,
ALL DIMENSIONS ARE GIVEN
IN INCHES, THIRD ANGLE PROJECTION.

DRAWN BY
DW

MAT'L:

SCALE

NONE

DATE
02-16-98

PVC

DRAWING NO.

36572-14

DWG

SIZE

REV	DATE	BY	CHK	DESCRIPTION	ECN	CHK	CUST	SUP
-	-----	---	--	E. REVISED PART WEIGHT: WAS PER 10 PCS	-----	----	----	
3	06-11-04	JBN	PM	D. ADDED NOTE #5 C. ADDED PART NUMBER OF70PG	36572-14	RGRO	RGRO	
2	03-13-00	JHNU	HIW	B. REV'D NOTE 2: ADDED TG-70	36572-14	HIW	HIW	
1	06-30-99	DW	HIW	A. REVISED TITLE NAME.	36572-14	HIW	HIW	
R	02-16-98	DW	HIW	RELEASED TO PRODUCTION.	36572-14	HIW	HIW	