

# STI WIRELESS RECEIVERS




STI-34104



STI-34108



STI-34098



STI-34188



STI-V34104

## PRODUCT OVERVIEW

The receivers allow you to monitor up to 8 different STI wireless alert devices at a single, convenient location. Supervised for low battery and signal reception, they have an audible chime tone or 12 VDC output for siren. The 4-Channel Voice Receiver sounds a tune or a prerecorded programmable voice message. Offers ten tones/tunes or 53 selectable words (English or Spanish) to create a custom message up to four words. The 8-Channel Receiver offers a mirror function that can work with up to four additional 8-Channel Receivers. Devices can be latching or momentary by zone. STI offers multiple wireless products designed to alert you of several different conditions (such as: an open garage door, mail delivered, a car in the driveway, open exit door, removed fire extinguisher or activated push button, etc.).

## HOW IT WORKS

The receivers (excludes Single Channel Slave) supervise transmitter battery and signal reception (low battery is indicated with a short beep between 12 and 24 hours of detection).

## KEY FEATURES

### General Information

- Monitor 4 or 8 devices at a single, convenient location.
- Supervised for low battery and signal reception.

### Installation

- Easy installation.

### Electronics

- Operates up to 1000' (line of sight), 433MHz.
- Audible chime tone and 12 volt output.
- Devices can be latching or momentary by each zone (STI-V34104 & STI-34108).
- Includes 12 volt power supply.

### Options

#### STI-34104

- Monitors up to 4 devices.
- Distinct beep and tone for each of the four devices.
- Latching memory LED (flashes until reset).
- Input power is 12 volt, 75mA.

#### STI-V34104

- Monitors up to 4 devices.
- Ten tones/tunes or 53 selectable words (English or Spanish).
- Words can be programmed in sets of up to four to create custom message.

#### STI-34108

- Monitors up to 8 devices with 8 zone LED indicators.
- Mirror function (works with up to 4 additional 8-Channel Receivers).
- Dual antennas for increased signal strength.
- Form "C" contact for remote monitoring.
- 300mA, 12 volt available for siren output (with 500mA, 12 volt supply).
- Measures 5 1/4 x 5 3/4 x 1 1/4".
- Key fob available for alert or on/off.

#### STI-34098

- Allows transmitters to connect to control panel.
- Measures: 2 1/4 H x 1 1/2 W x 1/2" D.

#### STI-34188

- 8-Zone Relay Board for STI-34108.
- 8 momentary Form "C" relay contacts rated 3A, 125 VAC, 3A 28VDC.
- Measures: 5 7/8 H x 2 W x 1/2" D.



For more information, call 1-800-888-4784 (4STI) or visit [www.sti-usa.com](http://www.sti-usa.com)



**Safety Technology International, Inc.**

# STI Wireless Receivers

Dimensions and Technical Information

## MODELS AVAILABLE

### Receivers

<b>STI-34104</b>	4-Channel Receiver
<b>STI-34108</b>	8-Channel Receiver
<b>STI-V34104</b>	4-Channel Voice Receiver
<b>STI-34098</b>	Single Channel Slave Receiver

### Sensors

<b>STI-34101</b>	Wireless Driveway Monitor Sensor (solar powered)
<b>STI-34151</b>	Wireless Driveway Monitor Sensor (battery powered)
<b>STI-34201</b>	Wireless Mailbox Alert Sensor
<b>STI-34301</b>	Wireless Garage Sentry Alert Sensor
<b>STI-34401</b>	Wireless Universal Alert Sensor
<b>STI-34501</b>	Wireless Door Entry Alert® Sensor
<b>STI-34601</b>	Wireless Doorbell Button Alert Sensor
<b>STI-34701</b>	Wireless Indoor Motion Detector Alert Sensor
<b>STI-34752</b>	Wireless Outdoor Motion Detector Alert Sensor
<b>STI-6200WIR</b>	Wireless Fire Extinguisher Theft Stopper® Sensor
<b>STI-6400WIR</b>	Wireless Exit Stopper® Door Alarm Sensor
<b>STI-6517B</b>	Wireless Stopper® Station Shield with Sound and Wireless Transmitter

### 4-Channel Receiver Kits

<b>STI-34100</b>	Wireless Driveway Monitor (solar powered)
<b>STI-34150</b>	Wireless Driveway Monitor (battery powered)
<b>STI-34200</b>	Wireless Mailbox Alert
<b>STI-34300</b>	Wireless Garage Sentry Alert
<b>STI-34400</b>	Wireless Universal Alert
<b>STI-34500</b>	Wireless Door Entry Alert®
<b>STI-34600</b>	Wireless Doorbell Button Alert
<b>STI-34700</b>	Wireless Indoor Motion Detector Alert

### Single Channel Slave Receiver Kits

<b>STI-34119</b>	Wireless Driveway Monitor (solar powered)
<b>STI-34159</b>	Wireless Driveway Monitor (battery powered)
<b>STI-34209</b>	Wireless Mailbox Alert
<b>STI-34309</b>	Wireless Garage Sentry® Alert
<b>STI-34409</b>	Wireless Universal Alert
<b>STI-34609</b>	Wireless Doorbell Button Alert
<b>STI-34709</b>	Wireless Indoor Motion Detector Alert
<b>STI-34759</b>	Wireless Outdoor Motion Detector Alert

## WARRANTY

### TESTING

**STI-34104, STI-34108, STI-V34104**

- CE
- FCC & IC Compliant

### 4-Channel Voice Receiver Kits

<b>STI-V34100</b>	Wireless Driveway Monitor (solar powered)
<b>STI-V34150</b>	Wireless Driveway Monitor (battery powered)
<b>STI-V34200</b>	Wireless Mailbox Alert
<b>STI-V34300</b>	Wireless Garage Sentry Alert
<b>STI-V34400</b>	Wireless Universal Alert
<b>STI-V34500</b>	Wireless Door Entry Alert®
<b>STI-V34600</b>	Wireless Doorbell Button Alert
<b>STI-V34700</b>	Wireless Indoor Motion Detector Alert
<b>STI-V34760</b>	Wireless Outdoor Motion Detector Alert

### Accessories

<b>STI-34099</b>	Single Channel Slave Receiver Case
<b>STI-34105</b>	Voltamax 12 VDC (500mA) power supply
<b>STI-30104</b>	Lamp Controller
<b>STI-30105</b>	Extended Antenna
<b>STI-34106</b>	Key Fob
<b>STI-34109</b>	Repeater - Extends Transmitter range up to 1000'
<b>STI-34188</b>	8-Zone Relay Board for STI-34108



**Safety Technology  
International, Inc.**

2306 Airport Road  
Waterford, Michigan  
48327, USA

Tel: 248-673-9898  
Fax: 248-673-1246  
Toll-free: 800-888-4784  
info@sti-usa.com  
www.sti-usa.com

Unit 49G Pipers Road  
Park Farm Industrial Estate  
Redditch, Worcestershire  
B98 0HU England

Tel: 44 (0) 1527 520 999  
Fax: 44 (0) 1527 501 999  
info@sti-europe.com  
www.sti-europe.com