



### Professional Solutions - Unrivalled Value

Double universal adjustable height ceiling mount for 37" to 63" flat panel screens, ideal for commercial or retail settings. Continuous tilt of 20° forward with locking knob, 360° rotation and 1" incremental drop lengths provide perfect screen positioning. Makes a secure installation quick and easy, simply hang the screens and turn the pre-assembled securing screws to lock in place. Compatible with all 1.5" NPT threaded pipe.

37" - 63" / 94cm-160cm

300 lb / 136 kg (150lb per screen)

#### ■ Various Screen Sizes

Fits most 37" to 63" flat panel screens weighing 150lb or less.

#### ■ Multi-angle Positioning

Up to 20° of continuous tilt and 360° rotation.

#### ■ Commercial Grade

Ideal for commercial and retail settings.

#### ■ Easy Installation

Pre-assembled securing screw makes installation fast and easy.

#### ■ Standard Interface

Mounts to any 1.5" NPT threaded pipe.

#### ■ Universal Design

Works with any hole pattern up to 723mm (28.5") x 501mm (19.8") in height.

#### ■ Included Hardware

Pre-sorted hardware pack for easy component selection and installation (hardware for installation to wood studs or concrete surfaces included).

### Functional Specifications

Tilt: +20°/-0°  
Rotation: 360°

Mounting Surfaces: 1.5" NPT Threaded connection.

Max Mounting Pattern:  
723mm (28.5") width  
501mm (19.8") height

Load Capacity: 300 LB / 136 KG

Warranty: Limited 10 Years


#### Universal Design

Works with any hole pattern up to 723mm (28.5") x 501mm (19.8") in height.




#### Mounting Surface

Standard 1.5" NPT threaded connection.



#### Tilt

0 to +20° tilt for optimal viewing angles.



#### Lateral Adjustment

Lateral adjustment functionality for positioning TV in the right spot on the wall. Extended verticals allows for a wider screen coverage within the size range.

#### Pre-Installed Securing Screws

Easy hook and secure installation and pre-assembled securing screw makes installation fast and easy.



#### Mounting Hardware


Complete set of screen mounting hardware, labeled for ease of use and ready to go.



# Single Flat Panel Ceiling Mount

For 37" to 63" (94-160cm) LCD and Plasma TV's

C63D (BLACK)




## Product Specifications

| PRODUCT WEIGHT    | LOAD CAPACITY                                | COLORS | FINISH                          | PACKAGE SIZE (WxHxD)                 | SHIP WEIGHT     | UPC CODE                      | PACKAGE CONTENTS                                 |
|-------------------|--|--------|---------------------------------|--------------------------------------|-----------------|-------------------------------|--|
| 24.5 lb (11.1 Kg) | 300 lb (136 kg) total<br>150 lb (68 kg) each | Black  | Scratch resistant powdercoating | 38" x 11" x 6"<br>966 x 267 x 140 mm | 26.2 lb (12 Kg) | C63D (Black)<br>0815885010873 | Mount, screen mounting hardware, product manual. |

## Package Specifications

## Mounting Interface

|  | Universal |      | VESA  |      |       |       |       |       |       |       |       |       |       |       |
|---|-----------|------|-------|------|-------|-------|-------|-------|-------|-------|-------|-------|-------|-------|
|   | Min       | Max  | W     | 75mm | 100mm | 200mm | 200mm | 300mm | 300mm | 400mm | 400mm | 400mm | 600mm | 600mm |
|   | W         | 31mm | 723mm | X    | X     | X     | X     | X     | X     | X     | X     | X     | X     | X     |
|   | H         | 31mm | 501mm | H    | 75mm  | 100mm | 100mm | 200mm | 200mm | 300mm | 200mm | 300mm | 400mm | 200mm |

## Accessories

### Suspended Ceiling Adapters



CAS1W

For mounting above a false ceiling tile. 13" of lateral shift for fast project adjustment. Compatible with all 1.5" NPT threaded pipe.



CAS2W

Replaces a standard 2' x 2' grid. 13" of lateral shift for fast project adjustment. Compatible with all 1.5" NPT threaded pipe.

### Structural Ceiling Adapters



CA1

Wood Single Joist / Concrete



CA2

Wood 16" Double Joist / Concrete



CA4

General Purpose 4x4"



CA8

General Purpose 8x8"

### Truss Ceiling Adapter



CAT3

Mounts to round, square and rectangular trusses from .75" up to 3" in diameter and is compatible with all 1.5" NPT threaded pipe.

### Vaulted Ceiling Adapter



CAV1

For installation on cathedral or vaulted ceilings. Adjusts up to 94° and is compatible with all 1.5" NPT threaded pipe.

### Unistrut Ceiling Adapters



CAU1

Bracket and hardware for mounting to single 1-5/8"x1-5/8" Unistrut.



CAU4


Bracket and hardware (4x4) for mounting to standard 1-5/8"x1-5/8" dual channels spaced on 2.25" centers.



CAU8

Bracket and hardware (8x8) for mounting to standard 1-5/8"x1-5/8" dual channels spaced on 6" centers.

### Unistrut Bolts



HU2 (2 Bolts) HU4 (4 Bolts)

3/8" bolts and spring nuts for mounting ceiling brackets to standard 1-5/8"x1-5/8".

### Fixed Columns

Static ceiling columns for use with all ceiling adapters using standard 1.5" NPT interfaces. Connectors (sold separately) give ability to extend drop lengths by connecting two or more columns. Cable management with a completely open interior.



| BLACK | DROP |
|-------|------|
| E06   | 6"   |
| E1    | 12"  |
| E018  | 18"  |
| E2    | 2'   |
| E3    | 3'   |
| E4    | 4'   |
| E5    | 5'   |
| E6    | 6'   |
| E7    | 7'   |
| E8    | 8'   |
| E9    | 9'   |
| E10   | 10'  |

### Adjustable Columns

Adjustable extension columns designed for use with all ceiling adapters using standard 1.5" NPT interfaces. Column allows for flexibility with quick 1" incremental drop length adjustments and cable management with a completely open interior. Connectors (sold separately) give ability to extend drop lengths by connecting two or more columns.



| BLACK   | DROP    |
|---------|---------|
| EA0611  | 6"-11"  |
| EA01218 | 12"-18" |
| EA01824 | 18"-24" |
| EA23    | 2'-3'   |
| EA24    | 2'-4'   |
| EA35    | 3'-5'   |
| EA46    | 4'-6'   |
| EA57    | 5'-7'   |
| EA68    | 6'-8'   |
| EA79    | 7'-9'   |
| EA810   | 8'-10'  |
| EA911   | 9'-11'  |
| EA1012  | 10'-12' |

Visit [crimsonav.com](http://crimsonav.com) to see the full line of vidamounts LCD/plasma, projector and TV/monitor mounts. © 2010 Crimson AV LLC. All rights reserved.