


2

1


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



PANDUIT P/N	WEIGHT
CB**-2G	.592 LB/10 PCS. (269.0 g/10 PCS.)

NOTES:

- **1. SEE CURRENT CATALOG FOR ADDITIONAL PART NUMBER SUFFIXES TO INDICATE COLOR AND OR PACKAGE QUANTITY.
2. FOUR (4) #6-32 X 1.00" SLOTTED OVAL HEAD SCREWS ARE INCLUDED WITH PARTS.
3. DIMENSIONS IN PARENTHESES ARE IN METRIC.
4. PART ACCEPTS FLAT, SLOPED, SLOPED RECESSED, AND BLANK INSERTS.



PART NUMBER	CB**-2G	PRODUCT SPEC/PKG SPEC	N/A
I.I. NUMBER	N/A	WORK INSTRUCTION	N/A
TITLE	CLASSIC SERIES DOUBLE GANG FACEPLATE FRAME		
ITEM REVISION NAME	CUSTOMER DRAWING		
DATASET FILE NAME	M00058BA/03.PRT		
	M00058BA_DC/03B.PRT		
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm]		MATERIAL:	
.X ± .XX ± .03 [.8]		ABS	
.XXX ± .010 [.3]		DRAWING NUMBER:	
ANGLES ±		00058-02	
THIRD ANGLE PROJECTION		SHT 1 OF 1	
DRAWN BY	DATE	CHK	SCALE
RCA	6-17-97	CEF	NONE
			SIZE
			A

REV	DATE	BY	CHK	APR	DESCRIPTION	ECN
5	6-28-13	MDJR	JSP	JSP	F. REVISED TITLE TO FACEPLATE FRAME. E. REMOVED PART NUMBERS FROM NOTE 4.	00058-02
4	11-14-12	BJN	JSP	JSP	D. UPDATED DRAWING FORMAT TO REFLECT NEW LOGO	00058-02
3	7-13-99	JSP	CEF	CEF	C. WAS "DESIGNER SERIES"	00058-02
2	9-17-97	JBA	CEF	CEF	B. REV'D TITLE: WAS DESIGNER SERIES DOUBLE VERTICAL BEZEL (CB-2G**)	00058-02
1	9-12-97	RCA	CEF	CEF	A. REV'D TITLE WAS CB DOUBLE BEZEL	00058-02
R	6-17-97	RCA	CEF	CEF	RELEASED TO PRODUCTION	00058-02

2

1