


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



1. VISIT OUR ON-LINE CATALOG AT [WWW.PANDUIT.COM](http://WWW.PANDUIT.COM) FOR A LIST OF CURRENT PARTS APPLICABLE FOR USE WITH THIS PRODUCT.
2. PRIMARY DIMENSIONS ARE IN MILLIMETERS.
3. RAIL ADJUSTMENT MEASUREMENTS ARE TAKEN FROM THE FRONT FACE OF EACH EQUIPMENT RAIL. INDEPENDENT ADJUSTABLE REAR EQUIPMENT MOUNTING RAILS (EIA) ADJUST FROM 65mm [2.6in] TO 357mm [14.05in] AND FROM 521mm [20.5in] TO 765mm [30.1in] WITH PDU BRACKETS AND CABLE MANAGEMENT FINGERS IN PLACE. REMOVING PDU BRACKETS AND OPTIONAL FINGERS INCREASES MAXIMUM E-RAIL SPAN TO 911mm [35.86in].
4. CAN BE USED WITH ANY 19" EIA STANDARD COMPONENT IN ADDITION TO ALL PANDUIT HORIZONTAL CABLE MANAGEMENT AND PATCH PANEL PRODUCTS.
5. EIA UNIVERSAL STANDARD HOLE PROGRESSION ON EQUIPMENT RAILS  
15.88mm [.625in], 15.88mm [.625in],  
12.70mm [.5in], 15.88mm [.625in],  
15.88mm [.625in], 12.7mm [.5in],...ETC.
6. PARTS SUPPLIED:  
-BASE CABINET  
-FRONT PERFORATED SINGLE HINGE DOOR (SEE CHART ON SHEET 2)  
-REAR PERFORATED SPLIT DOOR (SEE CHART ON SHEET 2)  
-EQUIPMENT RAILS FRONT & REAR (SEE CHART ON SHEET 2)  
-PDU BRACKETS (SEE CHART ON SHEET 2)  
-CASTERS (SEE CHART ON SHEET 2)  
-CABINET HARDWARE KIT  
-INSTRUCTION SHEET
7. RACK UNIT SPACING NUMERALS ARE CLEARLY PRINTED ON EQUIPMENT MOUNTING RAILS.
8. FULLY BONDED STRUCTURE WHEN ASSEMBLED PER INSTRUCTIONS.
9. STATIC LOAD RATING. 1360 Kg (3000 LBS)
10. ROLLING LOAD RATING. 1133 Kg (2500 LBS)
11. SINGLE POINT GROUND LOCATIONS AT TOP AND BOTTOM OF CABINET.
12. ALL CABINET RAILS ARE INSTALLED NUMBERS UP.
13. MAXIMUM EQUIPMENT DEPTH, 959mm [37.75].

01A	12-04-14	PBS	ADP	TCN	FLOOR MOUNT DIMENSIONS UPDATED	V09000BX	
00A	5-15-13	PBS	NAGL	JDWE	RELEASED TO PRODUCTION	12V352BE-DC	
REV	DATE	BY	CHK	APR	DESCRIPTION	ECN	

TITLE		NET-ACCESS S TYPE CABINET WITH VERTICAL PATCHING 600mm WIDE X 1070mm DEEP FAMILY CUSTOMER DRAWING					
ITEM REVISION NAME		12V352BE/01.PRT					
DATASET FILE NAME		12V352BE_DC/01A.PRT					
		MATERIAL:					
		N/A					
		DRAWING NUMBER:					
		12V352BE-DC					
DRAWN BY		DATE	CHK	SCALE			
PBS		5-15-13	NAGL	NONE	SHT 1 OF 5		
					SIZE		
					A		

2

1

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PART NO.	DESCRIPTION	SINGLE HINGE FRONT DOOR	SPLIT REAR DOOR	SPLIT SIDE PANEL	FRONT CAGE NUT E-RAIL	REAR CAGE NUT FINGER MGMT E-RAIL	REAR CAGE NUT VERTICAL PATCH E-RAIL	STANDARD PDU BRACKETS	CASTERS	CABLE MGMT FINGERS	CABINET WEIGHT FULLY UNPACKAGED	CABINET WEIGHT SHIPPING WEIGHT
S6212*P	NET-ACCESS S-TYPE CABINET 600mm X 42RU X 1070mm DEEP	01	01	02	02	00	02	02	04	00	116 Kg/EACH 257 LBS/EACH	136 Kg/EACH 302 LBS/EACH
S6512*P	NET-ACCESS S-TYPE CABINET 600mm X 45RU X 1070mm DEEP	01	01	02	02	00	02	02	04	00	121 Kg/EACH 267 LBS/EACH	141 Kg/EACH 312 LBS/EACH
S6812*P	NET-ACCESS S-TYPE CABINET 600mm X 48RU X 1070mm DEEP	01	01	02	02	00	02	02	04	00	125 Kg/EACH 277 LBS/EACH	146 Kg/EACH 322 LBS/EACH
S6219*P	NET-ACCESS S-TYPE CABINET 600mm X 42RU X 1070mm DEEP	01	01	00	02	00	02	02	04	00	129 Kg/EACH 184 LBS/EACH	104 Kg/EACH 229 LBS/EACH
S6519*P	NET-ACCESS S-TYPE CABINET 600mm X 45RU X 1070mm DEEP	01	01	00	02	00	02	02	04	00	86 Kg/EACH 189 LBS/EACH	106 Kg/EACH 234 LBS/EACH
S6819*P	NET-ACCESS S-TYPE CABINET 600mm X 48RU X 1070mm DEEP	01	01	00	02	00	02	02	04	00	88 Kg/EACH 194 LBS/EACH	108 Kg/EACH 238 LBS/EACH



\* DENOTES COLOR

"B" = BLACK

"W" = WHITE

A

A

							TITLE NET-ACCESS S TYPE CABINET WITH VERTICAL PATCHING 600mm WIDE X 1070mm DEEP FAMILY CUSTOMER DRAWING					
							ITEM REVISION NAME 12V352BE/01.PRT					
							DATASET FILE NAME 12V352BE_DC/01A.PRT					
											MATERIAL:  N/A	
01A	12-04-14	PBS	ADP	TCN	SEE SHEET 1 OF 5 FOR REVISIONS	V09000BX					DRAWING NUMBER: 12V352BE - DC	
00A	5-15-13	PBS	NAGL	JDWE	SEE SHEET 1 OF 5 FOR REVISIONS	12V352BE-DC	 THIRD ANGLE PROJECTION					
REV	DATE	BY	CHK	APR	DESCRIPTION	ECN	DRAWN BY PBS	DATE 5-15-13	CHK NAGL	SCALE NONE	SHT 2 OF 5	SIZE A


2


1

2

1

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.




							TITLE					
							NET-ACCESS S TYPE CABINET WITH VERTICAL PATCHING 600mm WIDE X 1070mm DEEP FAMILY CUSTOMER DRAWING					
							ITEM REVISION NAME 12V352BE/01.PRT			<div>PANDUIT</div>		
							DATASET FILE NAME 12V352BE_DC/01A.PRT					
										MATERIAL:  N/A		
01A	12-04-14	PBS	ADP	TCN	SEE SHEET 1 OF 5 FOR REVISIONS	V09000BX	<div></div> THIRD ANGLE PROJECTION			DRAWING NUMBER: 12V352BE-DC		
00A	5-15-13	PBS	NAGL	JDWE	SEE SHEET 1 OF 5 FOR REVISIONS	12V352BE-DC						
REV	DATE	BY	CHK	APR	DESCRIPTION	ECN	DRAWN BY	DATE	CHK	SCALE	SHT 3 OF 5	SIZE A
							PBS	5-15-13	NAGL	NONE		


2

1


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.





FRONT DOOR, REAR DOOR, AND SIDE PANELS NOT SHOWN

							TITLE NET-ACCESS S TYPE CABINET WITH VERTICAL PATCHING 600mm WIDE X 1070mm DEEP FAMILY CUSTOMER DRAWING					
							ITEM REVISION NAME 12V352BE/01.PRT		<div>PANDUIT</div>			
							DATASET FILE NAME 12V352BE_DC/01A.PRT					
									MATERIAL:  N/A			
01A	12-04-14	PBS	ADP	TCN	SEE SHEET 1 OF 5 FOR REVISIONS	V09000BX	<div></div> THIRD ANGLE PROJECTION		DRAWING NUMBER: 12V352BE - DC			
00A	5-15-13	PBS	NAGL	JDWE	SEE SHEET 1 OF 5 FOR REVISIONS	12V352BE-DC						
REV	DATE	BY	CHK	APR	DESCRIPTION	ECN	DRAWN BY PBS	DATE 5-15-13	CHK NAGL	SCALE NONE	SHT 4 OF 5	SIZE A

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



FLOOR MOUNTING HOLE LOCATIONS - SOME PARTS REMOVED FOR CLARITY

							TITLE NET-ACCESS S TYPE CABINET WITH VERTICAL PATCHING 600mm WIDE X 1070mm DEEP FAMILY CUSTOMER DRAWING						
							ITEM REVISION NAME 12V352BE/01.PRT						
							DATASET FILE NAME 12V352BE_DC/01A.PRT						
											MATERIAL:  N/A		
01A	12-04-14	PBS	ADP	TCN	SEE SHEET 1 OF 5 FOR REVISIONS	V09000BX	 THIRD ANGLE PROJECTION				DRAWING NUMBER: 12V352BE - DC		
00A	5-15-13	PBS	NAGL	JDWE	SEE SHEET 1 OF 5 FOR REVISIONS	12V352BE -DC							
REV	DATE	BY	CHK	APR	DESCRIPTION	ECN	DRAWN BY PBS	DATE 5-15-13	CHK NAGL	SCALE NONE	SHT 5 OF 5	SIZE A	