



THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



1. VISIT OUR ON-LINE CATALOG AT WWW.PANDUIT.COM FOR A LIST OF CURRENT PARTS APPLICABLE FOR USE WITH THIS PRODUCT.
2. PRIMARY DIMENSIONS ARE IN MILLIMETERS.
3. FACTORY SETTINGS:
 - FRONT FACE OF FRONT E-RAILS ARE 167mm [6.57in] FROM FRONT FACE OF FRAME.
 - FRONT FACE OF REAR E-RAILS ARE 412.75mm [16.25in] FROM FRONT FACE OF FRONT E-RAILS.
4. ADJUSTMENTS:
 - RAIL ADJUSTMENT MEASUREMENTS ARE TAKEN FROM THE FRONT FACE OF EACH EQUIPMENT RAIL.
 - FRONT E-RAILS CAN ADJUST AS FAR FORWARD AS 167mm [6.57in] FROM FRONT FACE OF FRAME.
 - WHEN FRONT E-RAILS ARE 167mm [6.57in] FROM FRONT FACE OF FRAME, REAR E-RAILS CAN ADJUST FROM 62mm [2.44in] TO 327mm [12.87in] AND FROM 359mm [14.13in] TO 766mm [30.16in].
5. CAN BE USED WITH ANY 19" EIA STANDARD COMPONENT IN ADDITION TO ALL PANDUIT HORIZONTAL CABLE MANAGEMENT AND PATCH PANEL PRODUCTS.
6. EIA UNIVERSAL STANDARD HOLE PROGRESSION ON EQUIPMENT RAILS
 - 15.88mm [.625in], 15.88mm [.625in], 12.70mm [.5in], 15.88mm [.625in], 15.88mm [.625in], 12.70mm [.5in]...ETC.
7. PARTS SUPPLIED:
 - BASE CABINET
 - FRONT PERFORATED SINGLE HINGE DOOR (SEE CHART ON SHEET 2)
 - REAR PERFORATED SPLIT DOOR (SEE CHART ON SHEET 2)
 - SPLIT SIDE PANELS (SEE CHART ON SHEET 2)
 - CAGE NUT UTILITY STYLE EQUIPMENT RAILS FRONT AND REAR (SEE CHART ON SHEET 2)
 - CASTERS (SEE CHART ON SHEET 2)
 - CABLE MANAGEMENT FINGERS (SEE CHART ON SHEET 2)
 - CABINET HARDWARE KIT
 - INSTRUCTION SHEET
8. RACK UNIT SPACING NUMERALS ARE CLEARLY PRINTED ON EQUIPMENT MOUNTING RAILS.
9. FULLY BONDED STRUCTURE WHEN ASSEMBLED PER INSTRUCTIONS.
10. STATIC LOAD RATING. 1360 Kg (3000 LBS)
11. ROLLING LOAD RATING. 1133 Kg (2500 LBS)
12. SINGLE POINT GROUND LOCATIONS AT TOP AND BOTTOM OF CABINET.
13. ALL CABINET RAILS ARE INSTALLED NUMBERS UP.

01A	11-26-14	PBS	ADP	TCN	FLOOR MOUNT DIMENSIONS UPDATED	V09000BX	
00A	6-06-13	MDCA	PBS	JDWE	RELEASED TO PRODUCTION	12V352BS-DC	
REV	DATE	BY	CHK	APR	DESCRIPTION	ECN	

TITLE				NET-ACCESS S TYPE UTILITY CABINET 800mm WIDE X 1070mm DEEP FAMILY	
CUSTOMER DRAWING					
ITEM REVISION NAME		12V352BS/01.PRT		PANDUIT	
DATASET FILE NAME		12V352BS_DC/01A.PRT			
		THIRD ANGLE PROJECTION		MATERIAL:	
				N/A	
				DRAWING NUMBER:	
		12V352BS-DC			
DRAWN BY	DATE	CHK	SCALE	SIZE	
MDCA	6-06-13	PBS	NONE	SHT 1 OF 5	A

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PART NO.	DESCRIPTION	SINGLE HINGE FRONT DOOR	SPLIT REAR DOOR	SPLIT SIDE PANEL	ADJUSTABLE FRONT UTILITY E-RAILS	REAR CAGE NUT FINGER MGMT E-RAILS	STANDARD PDU BRACKETS	CASTERS	CABLE MGMT FINGERS	CABINET WEIGHT FULLY UNPACKAGED	CABINET WEIGHT SHIPPING WEIGHT
S8212*A	NET-ACCESS S-TYPE CABINET 800mm X 42RU X 1070mm DEEP	01	01	02	02	02	00	04	01	142 Kg/EACH 315 LBS/EACH	163 Kg/EACH 360 LBS/EACH
S8512*A	NET-ACCESS S-TYPE CABINET 800mm X 45RU X 1070mm DEEP	01	01	02	02	02	00	04	01	149 Kg/EACH 330 LBS/EACH	170 Kg/EACH 375 LBS/EACH
S8812*A	NET-ACCESS S-TYPE CABINET 800mm X 48RU X 1070mm DEEP	01	01	02	02	02	00	04	01	156 Kg/EACH 345 LBS/EACH	176 Kg/EACH 390 LBS/EACH
S8219*A	NET-ACCESS S-TYPE CABINET 800mm X 42RU X 1070mm DEEP	01	01	00	02	02	00	04	01	120 Kg/EACH 265 LBS/EACH	140 Kg/EACH 310 LBS/EACH
S8519*A	NET-ACCESS S-TYPE CABINET 800mm X 45RU X 1070mm DEEP	01	01	00	02	02	00	04	01	127 Kg/EACH 280 LBS/EACH	147 Kg/EACH 325 LBS/EACH
S8819*A	NET-ACCESS S-TYPE CABINET 800mm X 48RU X 1070mm DEEP	01	01	00	02	02	00	04	01	133 Kg/EACH 295 LBS/EACH	154 Kg/EACH 340 LBS/EACH

* DENOTES COLOR

"B" = BLACK

"W" = WHITE

							TITLE					
							NET-ACCESS S TYPE UTILITY CABINET 800mm WIDE X 1070mm DEEP FAMILY					
							CUSTOMER DRAWING					
							ITEM REVISION NAME 12V352BS/01.PRT				<div>PANDUIT</div>	
							DATASET FILE NAME 12V352BS_DC/01A.PRT					
											MATERIAL:	
											N/A	
01A	11-26-14	PBS	ADP	TCN	SEE SHEET 1 OF 5 FOR REVISIONS	V09000BX	<div><div><div></div><div></div></div><div></div></div> <div>THIRD ANGLE PROJECTION</div>				DRAWING NUMBER:	
00A	6-06-13	MDCA	PBS	JDWE	SEE SHEET 1 OF 5 FOR REVISIONS	12V352BS-DC					12V352BS-DC	
REV	DATE	BY	CHK	APR	DESCRIPTION	ECN	DRAWN BY MDCA	DATE 6-06-13	CHK PBS	SCALE NONE	SHT 2 OF 5	SIZE A

2

1

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

1115 [43.9]

798
[31.4]

HEIGHT
WITH
CASTERS

42RU
2026
[79.8]

45RU
2159
[85.0]

48RU
2292
[90.2]


1068 [42.0]

TILE COVERAGE
DEPTH


LEFT VIEW

RIGID
FRONT
CASTERS

FRONT VIEW



RIGHT VIEW



SWIVEL
REAR
CASTERS

REAR VIEW

A

A

TITLE

NET-ACCESS S TYPE UTILITY CABINET
800mm WIDE X 1070mm DEEP FAMILY

CUSTOMER DRAWING

ITEM REVISION NAME

12V352BS/01.PRT

DATASET FILE NAME

12V352BS_DC/01A.PRT


PANDUIT

MATERIAL:

N/A

DRAWING NUMBER:

12V352BS-DC



THIRD ANGLE
PROJECTION

DRAWN BY

MDCA

DATE

6-06-13

CHK

PBS

SCALE

NONE

SHT 3 OF 5

SIZE


A

01A	11-26-14	PBS	ADP	TCN	SEE SHEET 1 OF 5 FOR REVISIONS	V09000BX
00A	6-06-13	MDCA	PBS	JDWE	SEE SHEET 1 OF 5 FOR REVISIONS	12V352BS-DC
REV	DATE	BY	CHK	APR	DESCRIPTION	ECN


2

1


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



FRONT DOOR, REAR DOOR,
AND SIDE PANELS NOT SHOWN

							TITLE NET-ACCESS S TYPE UTILITY CABINET 800mm WIDE X 1070mm DEEP FAMILY					
							CUSTOMER DRAWING					
							ITEM REVISION NAME 12V352BS/01.PRT				<div>PANDUIT</div>	
							DATASET FILE NAME 12V352BS_DC/01A.PRT					
											MATERIAL: N/A	
01A	11-26-14	PBS	ADP	TCN	SEE SHEET 1 OF 5 FOR REVISIONS	V09000BX	<div>THIRD ANGLE PROJECTION</div>				DRAWING NUMBER: 12V352BS-DC	
00A	6-06-13	MDCA	PBS	JDWE	SEE SHEET 1 OF 5 FOR REVISIONS	12V352BS-DC					SIZE A	
REV	DATE	BY	CHK	APR	DESCRIPTION	ECN	DRAWN BY MDCA	DATE 6-06-13	CHK PBS	SCALE NONE	SHT 4 OF 5	A

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



FLOOR MOUNTING HOLE LOCATIONS -
SOME PARTS REMOVED FOR CLARITY

							TITLE NET-ACCESS S TYPE UTILITY CABINET 800mm WIDE X 1070mm DEEP FAMILY						
							CUSTOMER DRAWING						
							ITEM REVISION NAME 12V352BS/01.PRT				<div>PANDUIT</div>		
							DATASET FILE NAME 12V352BS_DC/01A.PRT						
							<div><div><div></div><div></div></div><div>THIRD ANGLE PROJECTION</div></div>				MATERIAL: N/A		
01A	11-26-14	PBS	ADP	TCN	SEE SHEET 1 OF 5 FOR REVISIONS	V09000BX					DRAWING NUMBER: 12V352BS-DC		
00A	6-06-13	MDCA	PBS	JDWE	SEE SHEET 1 OF 5 FOR REVISIONS	12V352BS-DC							
REV	DATE	BY	CHK	APR	DESCRIPTION	ECN	DRAWN BY MDCA	DATE 6-06-13	CHK PBS	SCALE NONE	SHT 5 OF 5	SIZE A	